

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P843561

Luminaire Tested: **LD4C25DE010B50 EU4C25B50 4LBWLI**

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-08
Report Number: P843561
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208077)
Test Lab: INNOVATION CENTER
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C25DE010B50 EU4C25B50 4LBWLI
Description: 4in Downlight with BioUp LEDs
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2639.9 lumens
Efficiency: N/A
Efficacy: 88.6 lumens/watt
Spacing Criteria (0/90/45): 1.29 / 1.29 / 1.18
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 29.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P843561

CATALOG NUMBER: LD4C25DE010B50 EU4C25B50 4LBWLI

Luminous Intensity Polar Plot





TEST NUMBER: P843561

CATALOG NUMBER: LD4C25DE010B50 EU4C25B50 4LBWLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92	92	92	92
2	106	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84	84	84	84
3	100	93	87	83	98	92	86	82	89	85	81	86	83	80	84	81	78	77	77	77	77
4	94	86	79	75	92	84	79	74	82	77	73	80	76	72	78	75	72	70	70	70	70
5	88	79	72	68	87	78	72	67	76	71	67	74	70	66	73	69	65	64	64	64	64
6	83	73	66	62	82	72	66	61	71	65	61	69	64	60	68	63	60	58	58	58	58
7	78	68	61	56	77	67	61	56	66	60	56	64	59	55	63	59	55	54	54	54	54
8	74	63	56	52	72	62	56	51	61	55	51	60	55	51	59	54	51	49	49	49	49
9	69	59	52	48	68	58	52	47	57	51	47	56	51	47	55	50	47	45	45	45	45
10	66	55	48	44	65	54	48	44	53	48	44	53	47	44	52	47	43	42	42	42	42

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	198703
5°	202077
10°	211212
15°	224168
20°	233995
25°	231973
30°	215725
35°	184561
40°	140616
45°	82475
50°	35225
55°	10367
60°	2973
65°	1744
70°	1114
75°	1471
80°	0
85°	0



TEST NUMBER: P843561

CATALOG NUMBER: LD4C25DE010B50 EU4C25B50 4LBWLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	158.2	6.0
10°-20°	499.2	18.9
20°-30°	778.7	29.5
30°-40°	757.7	28.7
40°-50°	378.4	14.3
50°-60°	58.6	2.2
60°-70°	7.1	0.3
70°-80°	2.0	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1436.1	54.4
0°-40°	2193.8	83.1
0°-60°	2630.8	99.7
0°-90°	2639.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2639.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1617	
5°	1639	158
15°	1762	499
25°	1711	779
35°	1231	758
45°	475	378
55°	48	59
65°	6	7
75°	3	2
85°	0	0
90°	0	



TEST NUMBER: P843561

CATALOG NUMBER: LD4C25DE010B50 EU4C25B50 4LBWLI

CANDELA DISTRIBUTION (FULL):

0°	
0°	1617.4
2.5°	1623.5
5°	1638.6
7.5°	1662.8
10°	1693.1
12.5°	1732.3
15°	1762.5
17.5°	1786.8
20°	1789.8
22.5°	1768.7
25°	1711.3
27.5°	1626.5
30°	1520.7
32.5°	1387.8
35°	1230.6
37.5°	1058.1
40°	876.8
42.5°	683.3
45°	474.7
47.5°	305.3
50°	184.3
52.5°	99.7
55°	48.4
57.5°	21.2
60°	12.1
62.5°	9.1
65°	6.0
67.5°	6.0
70°	3.1
72.5°	3.1
75°	3.1
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)