

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P843261

Luminaire Tested: **LD4C08DE010B40 EU4C08B40 4LBMLI**

Issue Date: 2/17/2023

**Test Information**

Test Method: LM-79-08  
Report Number: P843261  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208178)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/17/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD4C08DE010B40 EU4C08B40 4LBMLI  
Description: 4in Downlight with BioUp LEDs  
Light Source: -  
Ballast/Driver:

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 765.8 lumens  
Efficiency: N/A  
Efficacy: 79.8 lumens/watt  
Spacing Criteria (0/90/45): 0.7 / 0.7 / 0.76  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 9.6  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P843261

CATALOG NUMBER: LD4C08DE010B40 EU4C08B40 4LBMLI

### Luminous Intensity Polar Plot





TEST NUMBER: P843261

CATALOG NUMBER: LD4C08DE010B40 EU4C08B40 4LBMLI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94			
2	109	104	100	97	107	102	99	96	99	96	94	96	94	92	94	92	90	88			
3	104	98	93	89	102	96	92	89	94	90	87	91	88	86	89	87	85	83			
4	99	92	87	83	97	91	86	82	89	85	81	87	83	80	85	82	79	78			
5	94	87	81	77	93	86	81	77	84	79	76	82	78	75	81	77	75	73			
6	90	82	76	72	89	81	76	72	80	75	71	78	74	71	77	73	70	69			
7	86	77	72	68	85	77	71	68	75	71	67	74	70	67	73	69	67	65			
8	82	73	68	64	81	73	67	64	72	67	64	71	66	63	70	66	63	62			
9	79	70	64	60	78	69	64	60	68	63	60	67	63	60	67	63	60	58			
10	75	66	61	57	74	66	61	57	65	60	57	64	60	57	64	60	57	56			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	148296
5°	145780
10°	133943
15°	112179
20°	89869
25°	72210
30°	53765
35°	30715
40°	14418
45°	6116
50°	1949
55°	1007
60°	663
65°	552
70°	359
75°	0
80°	0
85°	0



TEST NUMBER: P843261

CATALOG NUMBER: LD4C08DE010B40 EU4C08B40 4LBMLI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	109.3	14.3
10°-20°	244.3	31.9
20°-30°	243.0	31.7
30°-40°	132.3	17.3
40°-50°	30.6	4.0
50°-60°	4.3	0.6
60°-70°	1.6	0.2
70°-80°	0.4	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	596.6	77.9
0°-40°	728.9	95.2
0°-60°	763.8	99.7
0°-90°	765.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	765.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1207	
5°	1182	109
15°	882	244
25°	533	243
35°	205	132
45°	35	31
55°	5	4
65°	2	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P843261

CATALOG NUMBER: LD4C08DE010B40 EU4C08B40 4LBMLI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1207.1
2.5°	1204.3
5°	1182.1
7.5°	1136.7
10°	1073.7
12.5°	981.1
15°	882.0
17.5°	783.7
20°	687.4
22.5°	608.7
25°	532.7
27.5°	460.5
30°	379.0
32.5°	288.1
35°	204.8
37.5°	138.0
40°	89.9
42.5°	56.5
45°	35.2
47.5°	20.4
50°	10.2
52.5°	5.6
55°	4.7
57.5°	2.7
60°	2.7
62.5°	1.9
65°	1.9
67.5°	1.0
70°	1.0
72.5°	1.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)