

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P843275

Luminaire Tested: **LD4C08DE010B50 EU4C08B50 4LBMLI**

Issue Date: 2/17/2023



**Test Information**

Test Method: LM-79-08  
Report Number: P843275  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208178)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/17/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD4C08DE010B50 EU4C08B50 4LBMLI  
Description: 4in Downlight with BioUp LEDs  
Light Source: -  
Ballast/Driver:

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 817.6 lumens  
Efficiency: N/A  
Efficacy: 85.2 lumens/watt  
Spacing Criteria (0/90/45): 0.7 / 0.7 / 0.76  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 9.6  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P843275

CATALOG NUMBER: LD4C08DE010B50 EU4C08B50 4LBMLI

### Luminous Intensity Polar Plot





TEST NUMBER: P843275

CATALOG NUMBER: LD4C08DE010B50 EU4C08B50 4LBMLI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94																			
2	109	104	100	97	107	102	99	96	99	96	94	96	94	92	94	92	90	88																			
3	104	98	93	89	102	96	92	89	94	90	87	91	88	86	89	87	85	83																			
4	99	92	87	83	97	91	86	82	89	85	81	87	83	80	85	82	79	78																			
5	94	87	81	77	93	86	81	77	84	79	76	82	78	75	81	77	75	73																			
6	90	82	76	72	89	81	76	72	80	75	71	78	74	71	77	73	70	69																			
7	86	77	72	68	85	77	71	68	75	71	67	74	70	67	73	69	67	65																			
8	82	73	68	64	81	73	67	64	72	67	64	71	66	63	70	66	63	62																			
9	79	70	64	60	78	69	64	60	68	63	60	67	63	60	67	63	60	58																			
10	75	66	61	57	74	66	61	57	65	60	57	64	60	57	64	60	57	56																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	158334
5°	155646
10°	143012
15°	119760
20°	95949
25°	77103
30°	57382
35°	32785
40°	15380
45°	6550
50°	2083
55°	1071
60°	737
65°	581
70°	359
75°	0
80°	0
85°	0



TEST NUMBER: P843275

CATALOG NUMBER: LD4C08DE010B50 EU4C08B50 4LBMLI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	116.7	14.3
10°-20°	260.9	31.9
20°-30°	259.4	31.7
30°-40°	141.2	17.3
40°-50°	32.7	4.0
50°-60°	4.6	0.6
60°-70°	1.7	0.2
70°-80°	0.4	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	636.9	77.9
0°-40°	778.2	95.2
0°-60°	815.5	99.7
0°-90°	817.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	817.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1289	
5°	1262	117
15°	942	261
25°	569	259
35°	219	141
45°	38	33
55°	5	5
65°	2	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P843275

CATALOG NUMBER: LD4C08DE010B50 EU4C08B50 4LBMLI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1288.8
2.5°	1285.9
5°	1262.1
7.5°	1213.6
10°	1146.4
12.5°	1047.5
15°	941.6
17.5°	836.8
20°	733.9
22.5°	649.8
25°	568.8
27.5°	491.6
30°	404.5
32.5°	307.7
35°	218.6
37.5°	147.3
40°	95.9
42.5°	60.3
45°	37.7
47.5°	21.8
50°	10.9
52.5°	5.9
55°	5.0
57.5°	3.0
60°	3.0
62.5°	2.0
65°	2.0
67.5°	1.0
70°	1.0
72.5°	1.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)