

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P843277

Luminaire Tested: **LD4C08DE010B50 EU4C08B50 4LBNLI**

Issue Date: 2/16/2023



Test Information

Test Method: LM-79-08
Report Number: P843277
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208279)
Test Lab: INNOVATION CENTER
Issue Date: 2/16/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C08DE010B50 EU4C08B50 4LBNLI
Description: 4in Downlight with BioUp LEDs
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 642.0 lumens
Efficiency: N/A
Efficacy: 66.9 lumens/watt
Spacing Criteria (0/90/45): 0.48 / 0.48 / 0.54
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 9.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P843277

CATALOG NUMBER: LD4C08DE010B50 EU4C08B50 4LBNLI

Luminous Intensity Polar Plot





TEST NUMBER: P843277

CATALOG NUMBER: LD4C08DE010B50 EU4C08B50 4LBNLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95			95																
2	109	105	102	99	107	103	100	98	100	98	95	97	95	93	95	93	92	90			90																
3	105	99	95	92	103	98	94	91	95	92	89	93	90	88	91	89	87	85			85																
4	101	94	89	86	99	93	88	85	91	87	84	89	86	83	87	84	82	81			81																
5	96	89	84	80	95	88	84	80	87	82	79	85	81	79	83	80	78	77			77																
6	92	85	80	76	91	84	79	76	83	78	75	81	78	75	80	77	74	73			73																
7	89	81	76	72	88	80	75	72	79	75	71	78	74	71	77	73	71	69			69																
8	85	77	72	68	84	77	72	68	76	71	68	75	71	68	74	70	67	66			66																
9	82	74	69	65	81	73	68	65	72	68	65	72	68	65	71	67	64	63			63																
10	79	71	66	62	78	70	65	62	69	65	62	69	65	62	68	64	62	61			61																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	202966
5°	182653
10°	141602
15°	102488
20°	70965
25°	51727
30°	37578
35°	22242
40°	9366
45°	2919
50°	382
55°	214
60°	246
65°	291
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P843277

CATALOG NUMBER: LD4C08DE010B50 EU4C08B50 4LBNLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	130.2	20.3
10°-20°	222.9	34.7
20°-30°	177.1	27.6
30°-40°	93.8	14.6
40°-50°	16.2	2.5
50°-60°	1.2	0.2
60°-70°	0.6	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	530.2	82.6
0°-40°	624.0	97.2
0°-60°	641.4	99.9
0°-90°	642.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	642.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1652	
5°	1481	130
15°	806	223
25°	382	177
35°	148	94
45°	17	16
55°	1	1
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P843277

CATALOG NUMBER: LD4C08DE010B50 EU4C08B50 4LBNI

CANDELA DISTRIBUTION (FULL):

0°	
0°	1652.1
2.5°	1609.6
5°	1481.1
7.5°	1312.9
10°	1135.1
12.5°	963.0
15°	805.8
17.5°	659.4
20°	542.8
22.5°	453.8
25°	381.6
27.5°	323.3
30°	264.9
32.5°	205.6
35°	148.3
37.5°	97.9
40°	58.4
42.5°	33.6
45°	16.8
47.5°	5.9
50°	2.0
52.5°	2.0
55°	1.0
57.5°	1.0
60°	1.0
62.5°	1.0
65°	1.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)