

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P759933

Luminaire Tested: LD6D10D010-EU6DR150210IC9024-6LBDP1MW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P759933
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-21)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D10D010-EU6DR150210IC9024-6LBDP1MW
Description: 6 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 15° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 887.0 lumens
Efficiency: N/A
Efficacy: 75.8 lumens/watt
Spacing Criteria (0/90/45): 0.22 / 0.22 / 0.23
Luminous Opening: Vertical Cylinder (Dia: 0.35' x H: 0.35')
CIE Type: Direct

Input Watts (W): 11.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P759933
CATALOG NUMBER: LD6D10D010-EU6DR150210IC9024-6LBDP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P759933

CATALOG NUMBER: LD6D10D010-EU6DR150210IC9024-6LBDP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100															
1	116	114	112	111	113	112	110	109	108	107	106	104	103	103	101	100	100	98				98															
2	113	110	107	105	111	108	106	104	105	103	102	102	101	100	100	98	98	96				96															
3	110	106	103	101	108	105	102	100	103	100	99	100	99	97	98	97	96	94				94															
4	108	103	100	98	106	102	99	97	100	98	96	99	97	95	97	95	94	93				93															
5	106	101	98	95	104	100	97	95	98	96	94	97	95	93	96	94	92	92				92															
6	104	99	95	93	102	98	95	93	97	94	92	96	93	92	95	93	91	90				90															
7	102	97	94	91	101	96	93	91	95	93	91	94	92	90	93	91	90	89				89															
8	100	95	92	90	99	95	92	90	94	91	89	93	91	89	92	90	89	88				88															
9	99	93	90	88	98	93	90	88	92	90	88	92	89	88	91	89	88	87				87															
10	97	92	89	87	96	92	89	87	91	89	87	91	88	87	90	88	86	86				86															

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1359804	1359804	1359804
5°	799088	788742	794982
10°	238494	240164	243831
15°	59323	60478	58611
20°	17747	20554	18124
25°	6255	7969	6333
30°	2299	3025	2336
35°	1155	1300	1111
40°	724	802	724
45°	539	574	539
50°	424	424	424
55°	355	355	355
60°	288	288	288
65°	221	221	221
70°	190	190	190
75°	113	113	151
80°	79	79	79
85°	42	42	42

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°

Vertical Angle: 45°

Luminance: 574 cd/sqm



TEST NUMBER: P759933

CATALOG NUMBER: LD6D10D010-EU6DR150210IC9024-6LBDP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	575.3	64.9
10°-20°	236.6	26.7
20°-30°	47.0	5.3
30°-40°	11.7	1.3
40°-50°	6.2	0.7
50°-60°	4.6	0.5
60°-70°	3.3	0.4
70°-80°	1.8	0.2
80°-90°	0.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	858.9	96.8
0°-40°	870.6	98.2
0°-60°	881.4	99.4
0°-90°	887.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	887.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	12085	12085	12085	12085	12085	
5°	7863	7782	7761	7815	7822	574
15°	683	696	696	684	675	234
25°	80	91	102	91	81	42
35°	16	17	18	17	15	11
45°	8	8	8	8	8	6
55°	5	5	5	5	5	5
65°	3	3	3	3	3	3
75°	2	2	2	2	2	2
85°	0	0	0	0	0	1
90°	0	0	0	0	0	



TEST NUMBER: P759933

CATALOG NUMBER: LD6D10D010-EU6DR150210IC9024-6LBDP1MW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	12085.0	12085.0	12085.0	12085.0	12085.0
2.5°	10901.2	10910.4	10913.9	10924.7	10964.6
5°	7862.8	7781.9	7761.0	7814.7	7822.4
7.5°	4657.6	4674.0	4733.8	4747.1	4699.0
10°	2556.0	2576.9	2573.9	2592.3	2613.2
12.5°	1307.1	1290.8	1285.6	1306.6	1277.5
15°	683.0	695.8	696.3	684.0	674.8
17.5°	367.3	382.2	406.7	386.8	356.1
20°	216.9	230.2	251.2	234.8	221.5
22.5°	134.0	144.8	159.6	146.8	136.1
25°	80.3	91.1	102.3	90.6	81.3
27.5°	47.6	56.8	63.9	56.3	47.1
30°	30.7	35.8	40.4	35.3	31.2
32.5°	21.5	23.5	25.6	23.5	21.5
35°	15.9	16.9	17.9	16.9	15.3
37.5°	12.3	13.3	13.8	12.8	11.8
40°	10.2	10.7	11.3	10.7	10.2
42.5°	8.7	9.2	9.2	9.2	8.7
45°	7.7	7.7	8.2	7.7	7.7
47.5°	6.7	6.7	7.2	6.7	6.7
50°	6.1	6.1	6.1	6.1	6.1
52.5°	5.6	5.6	5.6	5.6	5.6
55°	5.1	5.1	5.1	5.1	5.1
57.5°	4.6	4.6	4.6	4.6	4.6
60°	4.1	4.1	4.1	4.1	4.1
62.5°	3.6	3.6	3.6	3.6	3.6
65°	3.1	3.1	3.1	3.1	3.1
67.5°	3.1	3.1	3.1	3.1	3.1
70°	2.6	2.6	2.6	2.6	2.6
72.5°	2.0	2.0	2.0	2.0	2.0
75°	1.5	1.5	1.5	1.5	2.0
77.5°	1.5	1.5	1.5	1.5	1.5
80°	1.0	1.0	1.0	1.0	1.0
82.5°	1.0	1.0	1.0	1.0	1.0
85°	0.5	0.5	0.5	0.5	0.5
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - - 90°-270°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)