

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P760323

Luminaire Tested: LD6D10D010-EU6DR400210IC9024-6LBDP1MW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P760323
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-28)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D10D010-EU6DR400210IC9024-6LBDP1MW
Description: 6 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 40° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 898.0 lumens
Efficiency: N/A
Efficacy: 76.8 lumens/watt
Spacing Criteria (0/90/45): 0.68 / 0.68 / 0.6
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 11.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P760323
CATALOG NUMBER: LD6D10D010-EU6DR400210IC9024-6LBDP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P760323

CATALOG NUMBER: LD6D10D010-EU6DR400210IC9024-6LBDP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20																	
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																								
RCR																																																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																																				
1	115	112	110	108	112	110	108	107	106	105	103	103	101	100	99	98	97	96																																				
2	110	106	103	100	108	105	102	99	102	99	97	99	97	95	96	95	93	92																																				
3	106	101	97	94	104	100	96	93	97	94	92	95	93	90	93	91	89	88																																				
4	102	97	92	89	101	95	91	88	93	90	87	92	89	86	90	87	85	84																																				
5	99	92	88	84	97	91	87	84	90	86	83	88	85	83	87	84	82	81																																				
6	95	88	84	80	94	88	83	80	86	82	80	85	82	79	84	81	79	77																																				
7	92	85	80	77	91	84	80	77	83	79	76	82	79	76	81	78	76	74																																				
8	89	82	77	74	88	81	77	74	80	76	73	79	76	73	78	75	73	72																																				
9	86	79	74	71	85	78	74	71	77	73	71	77	73	70	76	72	70	69																																				
10	83	76	71	68	82	75	71	68	75	71	68	74	70	68	73	70	68	67																																				

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	228464
5°	227352
10°	214892
15°	182681
20°	124517
25°	51948
30°	16338
35°	7589
40°	4193
45°	1916
50°	935
55°	514
60°	262
65°	78
70°	32
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1916 cd/sqm



TEST NUMBER: P760323

CATALOG NUMBER: LD6D10D010-EU6DR400210IC9024-6LBDP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	193.6	21.6
10°-20°	433.6	48.3
20°-30°	217.1	24.2
30°-40°	39.8	4.4
40°-50°	11.0	1.2
50°-60°	2.6	0.3
60°-70°	0.5	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	844.2	94.0
0°-40°	884.0	98.4
0°-60°	897.6	99.9
0°-90°	898.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	898.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2091	
5°	2073	194
15°	1615	434
25°	431	217
35°	57	40
45°	12	11
55°	3	3
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P760323

CATALOG NUMBER: LD6D10D010-EU6DR400210IC9024-6LBDP1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	2091.0
2.5°	2087.9
5°	2072.9
7.5°	2025.0
10°	1936.9
12.5°	1799.6
15°	1615.0
17.5°	1375.0
20°	1070.9
22.5°	730.1
25°	430.9
27.5°	227.8
30°	129.5
32.5°	83.7
35°	56.9
37.5°	40.7
40°	29.4
42.5°	20.2
45°	12.4
47.5°	8.0
50°	5.5
52.5°	3.9
55°	2.7
57.5°	1.7
60°	1.2
62.5°	0.7
65°	0.3
67.5°	0.2
70°	0.1
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)