

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P757903

Luminaire Tested: LD6D05D010-EU6DR150210IC9024-6LBDP1H

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P757903
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-21)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D05D010-EU6DR150210IC9024-6LBDP1H
Description: 6 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 15° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 582.3 lumens
Efficiency: N/A
Efficacy: 77.6 lumens/watt
Spacing Criteria (0/90/45): 0.22 / 0.22 / 0.23
Luminous Opening: Vertical Cylinder (Dia: 0.35' x H: 0.35')
CIE Type: Direct

Input Watts (W): 7.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P757903

CATALOG NUMBER: LD6D05D010-EU6DR150210IC9024-6LBDP1H

Luminous Intensity Polar Plot





TEST NUMBER: P757903

CATALOG NUMBER: LD6D05D010-EU6DR150210IC9024-6LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						100													
1	116	114	112	111	113	112	110	109	108	107	106	104	103	103	101	100	100	98						98													
2	113	110	107	105	111	108	106	104	105	103	102	102	101	100	100	98	98	96						96													
3	110	106	103	101	108	105	102	100	103	100	99	100	99	97	98	97	96	94						94													
4	108	103	100	98	106	102	99	97	100	98	96	99	97	95	97	95	94	93						93													
5	106	101	98	95	104	100	97	95	98	96	94	97	95	93	96	94	92	92						92													
6	104	99	95	93	102	98	95	93	97	94	92	96	93	92	95	93	91	90						90													
7	102	97	94	91	101	96	93	91	95	93	91	94	92	90	93	91	90	89						89													
8	100	95	92	90	99	95	92	90	94	91	89	93	91	89	92	90	89	88						88													
9	99	93	90	88	98	93	90	88	92	90	88	92	89	88	91	89	88	87						87													
10	97	92	89	87	96	92	89	87	91	89	87	91	88	87	90	88	86	86						86													

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	892632	892632	892632
5°	524558	517759	521854
10°	156551	157653	160069
15°	38938	39702	38478
20°	11652	13493	11897
25°	4105	5235	4160
30°	1513	1984	1535
35°	755	857	733
40°	476	526	476
45°	350	378	350
50°	278	278	278
55°	237	237	237
60°	190	190	190
65°	143	143	143
70°	124	124	124
75°	76	76	98
80°	55	55	55
85°	25	25	25

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°

Vertical Angle: 45°

Luminance: 378 cd/sqm



TEST NUMBER: P757903

CATALOG NUMBER: LD6D05D010-EU6DR150210IC9024-6LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	377.6	64.9
10°-20°	155.3	26.7
20°-30°	30.9	5.3
30°-40°	7.7	1.3
40°-50°	4.0	0.7
50°-60°	3.0	0.5
60°-70°	2.1	0.4
70°-80°	1.2	0.2
80°-90°	0.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	563.8	96.8
0°-40°	571.5	98.2
0°-60°	578.6	99.4
0°-90°	582.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	582.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	7933	7933	7933	7933	7933	
5°	5162	5108	5095	5130	5135	377
15°	448	457	457	449	443	154
25°	53	60	67	59	53	28
35°	10	11	12	11	10	7
45°	5	5	5	5	5	4
55°	3	3	3	3	3	3
65°	2	2	2	2	2	2
75°	1	1	1	1	1	1
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P757903

CATALOG NUMBER: LD6D05D010-EU6DR150210IC9024-6LBDP1H

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	7933.1	7933.1	7933.1	7933.1	7933.1
2.5°	7156.0	7162.0	7164.4	7171.4	7197.6
5°	5161.5	5108.4	5094.6	5129.9	5134.9
7.5°	3057.5	3068.2	3107.5	3116.2	3084.7
10°	1677.8	1691.6	1689.6	1701.7	1715.5
12.5°	858.1	847.3	844.0	857.7	838.6
15°	448.3	456.7	457.1	449.0	443.0
17.5°	241.1	250.9	267.0	253.9	233.7
20°	142.4	151.1	164.9	154.1	145.4
22.5°	88.0	95.0	104.8	96.4	89.3
25°	52.7	59.8	67.2	59.4	53.4
27.5°	31.2	37.3	42.0	36.9	30.9
30°	20.2	23.5	26.5	23.2	20.5
32.5°	14.1	15.4	16.8	15.4	14.1
35°	10.4	11.1	11.8	11.1	10.1
37.5°	8.1	8.7	9.1	8.4	7.7
40°	6.7	7.1	7.4	7.1	6.7
42.5°	5.7	6.0	6.0	6.0	5.7
45°	5.0	5.0	5.4	5.0	5.0
47.5°	4.4	4.4	4.7	4.4	4.4
50°	4.0	4.0	4.0	4.0	4.0
52.5°	3.7	3.7	3.7	3.7	3.7
55°	3.4	3.4	3.4	3.4	3.4
57.5°	3.0	3.0	3.0	3.0	3.0
60°	2.7	2.7	2.7	2.7	2.7
62.5°	2.4	2.4	2.4	2.4	2.4
65°	2.0	2.0	2.0	2.0	2.0
67.5°	2.0	2.0	2.0	2.0	2.0
70°	1.7	1.7	1.7	1.7	1.7
72.5°	1.3	1.3	1.3	1.3	1.3
75°	1.0	1.0	1.0	1.0	1.3
77.5°	1.0	1.0	1.0	1.0	1.0
80°	0.7	0.7	0.7	0.7	0.7
82.5°	0.7	0.7	0.7	0.7	0.7
85°	0.3	0.3	0.3	0.3	0.3
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - - 90°-270°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)