

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P760729

Luminaire Tested: LD6D10D010-EU6DR650210IC9027-6LBS1LI

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P760729
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D10D010-EU6DR650210IC9027-6LBS1LI
Description: 6 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 974.8 lumens
Efficiency: N/A
Efficacy: 83.3 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct

Input Watts (W): 11.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P760729
CATALOG NUMBER: LD6D10D010-EU6DR650210IC9027-6LBS1LI

Luminous Intensity Polar Plot





TEST NUMBER: P760729

CATALOG NUMBER: LD6D10D010-EU6DR650210IC9027-6LBS1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93																			
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85																			
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78																			
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72																			
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66																			
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61																			
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56																			
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52																			
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49																			
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	51699
5°	51562
10°	51524
15°	49931
20°	45458
25°	39612
30°	32951
35°	26109
40°	18839
45°	11902
50°	6206
55°	3299
60°	1729
65°	954
70°	393
75°	429
80°	303
85°	268

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 11902 cd/sqm



TEST NUMBER: P760729

CATALOG NUMBER: LD6D10D010-EU6DR650210IC9027-6LBS1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	83.7	8.6
10°-20°	229.2	23.5
20°-30°	280.2	28.7
30°-40°	227.4	23.3
40°-50°	113.3	11.6
50°-60°	31.6	3.2
60°-70°	7.2	0.7
70°-80°	1.8	0.2
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	593.1	60.8
0°-40°	820.5	84.2
0°-60°	965.3	99.0
0°-90°	974.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	974.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	885	
5°	880	84
15°	826	229
25°	615	280
35°	366	227
45°	144	113
55°	32	32
65°	7	7
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P760729

CATALOG NUMBER: LD6D10D010-EU6DR650210IC9027-6LBS1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	885.2
2.5°	884.5
5°	879.5
7.5°	876.7
10°	868.8
12.5°	852.6
15°	825.8
17.5°	783.9
20°	731.4
22.5°	674.6
25°	614.7
27.5°	550.6
30°	488.6
32.5°	427.3
35°	366.2
37.5°	305.2
40°	247.1
42.5°	192.7
45°	144.1
47.5°	100.4
50°	68.3
52.5°	47.1
55°	32.4
57.5°	21.8
60°	14.8
62.5°	10.3
65°	6.9
67.5°	3.5
70°	2.3
72.5°	2.2
75°	1.9
77.5°	1.3
80°	0.9
82.5°	0.6
85°	0.4
87.5°	0.3
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)