

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P759957

Luminaire Tested: LD6D10D010-EU6DR150210IC9030-6LBDP1H

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P759957
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-21)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D10D010-EU6DR150210IC9030-6LBDP1H
Description: 6 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 15° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1049.6 lumens
Efficiency: N/A
Efficacy: 89.7 lumens/watt
Spacing Criteria (0/90/45): 0.22 / 0.22 / 0.23
Luminous Opening: Vertical Cylinder (Dia: 0.35' x H: 0.35')
CIE Type: Direct

Input Watts (W): 11.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P759957

CATALOG NUMBER: LD6D10D010-EU6DR150210IC9030-6LBDP1H

Luminous Intensity Polar Plot





TEST NUMBER: P759957

CATALOG NUMBER: LD6D10D010-EU6DR150210IC9030-6LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						100													
1	116	114	112	111	113	112	110	109	108	107	106	104	103	103	101	100	100	98						98													
2	113	110	107	105	111	108	106	104	105	103	102	102	101	100	100	98	98	96						96													
3	110	106	103	101	108	105	102	100	103	100	99	100	99	97	98	97	96	94						94													
4	108	103	100	98	106	102	99	97	100	98	96	99	97	95	97	95	94	93						93													
5	106	101	98	95	104	100	97	95	99	96	94	97	95	93	96	94	92	92						92													
6	104	99	95	93	102	98	95	93	97	94	92	96	93	92	95	93	91	90						90													
7	102	97	94	91	101	96	93	91	95	93	91	94	92	90	93	91	90	89						89													
8	100	95	92	90	99	95	92	90	94	91	89	93	91	89	92	90	89	88						88													
9	99	93	90	88	98	93	90	88	92	90	88	92	89	88	91	89	88	87						87													
10	97	92	89	87	96	92	89	87	91	89	87	91	88	87	90	88	86	86						86													

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1609215	1609215	1609215
5°	945657	933411	940789
10°	282237	284215	288563
15°	70206	71570	69364
20°	21004	24326	21454
25°	7408	9434	7502
30°	2718	3579	2763
35°	1365	1540	1322
40°	859	944	859
45°	637	679	637
50°	508	508	508
55°	425	425	425
60°	337	337	337
65°	257	257	257
70°	219	219	219
75°	136	136	181
80°	95	95	95
85°	50	50	50

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°

Vertical Angle: 45°

Luminance: 679 cd/sqm



TEST NUMBER: P759957

CATALOG NUMBER: LD6D10D010-EU6DR150210IC9030-6LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	680.8	64.9
10°-20°	280.0	26.7
20°-30°	55.6	5.3
30°-40°	13.9	1.3
40°-50°	7.3	0.7
50°-60°	5.4	0.5
60°-70°	3.8	0.4
70°-80°	2.2	0.2
80°-90°	0.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1016.4	96.8
0°-40°	1030.3	98.2
0°-60°	1043.0	99.4
0°-90°	1049.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1049.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	14302	14302	14302	14302	14302	
5°	9305	9209	9184	9248	9257	680
15°	808	823	824	810	799	277
25°	95	108	121	107	96	50
35°	19	20	21	20	18	13
45°	9	9	10	9	9	7
55°	6	6	6	6	6	5
65°	4	4	4	4	4	4
75°	2	2	2	2	2	2
85°	1	1	1	1	1	1
90°	0	0	0	0	0	



TEST NUMBER: P759957

CATALOG NUMBER: LD6D10D010-EU6DR150210IC9030-6LBDP1H

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	14301.6	14301.6	14301.6	14301.6	14301.6
2.5°	12900.7	12911.6	12915.8	12928.5	12975.7
5°	9305.0	9209.3	9184.5	9248.1	9257.1
7.5°	5511.9	5531.3	5602.1	5617.9	5560.9
10°	3024.8	3049.6	3046.0	3067.8	3092.6
12.5°	1546.9	1527.5	1521.5	1546.3	1511.8
15°	808.3	823.4	824.0	809.5	798.6
17.5°	434.7	452.3	481.3	457.7	421.4
20°	256.7	272.4	297.3	277.9	262.2
22.5°	158.6	171.3	188.9	173.8	161.0
25°	95.1	107.8	121.1	107.2	96.3
27.5°	56.3	67.2	75.7	66.6	55.7
30°	36.3	42.4	47.8	41.8	36.9
32.5°	25.4	27.9	30.3	27.9	25.4
35°	18.8	20.0	21.2	20.0	18.2
37.5°	14.5	15.7	16.3	15.1	13.9
40°	12.1	12.7	13.3	12.7	12.1
42.5°	10.3	10.9	10.9	10.9	10.3
45°	9.1	9.1	9.7	9.1	9.1
47.5°	7.9	7.9	8.5	7.9	7.9
50°	7.3	7.3	7.3	7.3	7.3
52.5°	6.7	6.7	6.7	6.7	6.7
55°	6.1	6.1	6.1	6.1	6.1
57.5°	5.4	5.4	5.4	5.4	5.4
60°	4.8	4.8	4.8	4.8	4.8
62.5°	4.2	4.2	4.2	4.2	4.2
65°	3.6	3.6	3.6	3.6	3.6
67.5°	3.6	3.6	3.6	3.6	3.6
70°	3.0	3.0	3.0	3.0	3.0
72.5°	2.4	2.4	2.4	2.4	2.4
75°	1.8	1.8	1.8	1.8	2.4
77.5°	1.8	1.8	1.8	1.8	1.8
80°	1.2	1.2	1.2	1.2	1.2
82.5°	1.2	1.2	1.2	1.2	1.2
85°	0.6	0.6	0.6	0.6	0.6
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - - 90°-270°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)