

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P760815

Luminaire Tested: LD6D10D010-EU6DR700210IC9030-6LBDP1H

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P760815
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D10D010-EU6DR700210IC9030-6LBDP1H
Description: 6 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1049.2 lumens
Efficiency: N/A
Efficacy: 89.7 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 11.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P760815

CATALOG NUMBER: LD6D10D010-EU6DR700210IC9030-6LBDP1H

Luminous Intensity Polar Plot





TEST NUMBER: P760815

CATALOG NUMBER: LD6D10D010-EU6DR700210IC9030-6LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	128873
5°	125044
10°	121564
15°	119959
20°	112017
25°	84160
30°	59486
35°	21074
40°	11082
45°	11805
50°	12222
55°	12458
60°	12543
65°	12254
70°	11564
75°	10723
80°	9501
85°	7772

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 60°
 Luminance: 12543 cd/sqm



TEST NUMBER: P760815

CATALOG NUMBER: LD6D10D010-EU6DR700210IC9030-6LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	107.5	10.2
10°-20°	295.0	28.1
20°-30°	324.9	31.0
30°-40°	124.1	11.8
40°-50°	58.6	5.6
50°-60°	58.3	5.6
60°-70°	46.6	4.4
70°-80°	26.8	2.6
80°-90°	7.3	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	727.4	69.3
0°-40°	851.5	81.2
0°-60°	968.4	92.3
0°-90°	1049.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1049.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1180	
5°	1140	108
15°	1060	295
25°	698	325
35°	158	124
45°	76	59
55°	65	58
65°	47	47
75°	25	27
85°	6	7
90°	0	



TEST NUMBER: P760815

CATALOG NUMBER: LD6D10D010-EU6DR700210IC9030-6LBDP1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	1179.5
2.5°	1167.2
5°	1140.1
7.5°	1117.5
10°	1095.7
12.5°	1077.1
15°	1060.5
17.5°	1020.4
20°	963.4
22.5°	840.6
25°	698.1
27.5°	607.7
30°	471.5
32.5°	304.6
35°	158.0
37.5°	85.4
40°	77.7
42.5°	77.1
45°	76.4
47.5°	74.7
50°	71.9
52.5°	68.7
55°	65.4
57.5°	61.6
60°	57.4
62.5°	52.5
65°	47.4
67.5°	41.8
70°	36.2
72.5°	30.7
75°	25.4
77.5°	20.0
80°	15.1
82.5°	10.7
85°	6.2
87.5°	2.4
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)