

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P759972

Luminaire Tested: LD6D10D010-EU6DR150210IC9035-6LBDP1MW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P759972
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-21)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D10D010-EU6DR150210IC9035-6LBDP1MW
Description: 6 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 15° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1073.3 lumens
Efficiency: N/A
Efficacy: 91.7 lumens/watt
Spacing Criteria (0/90/45): 0.22 / 0.22 / 0.23
Luminous Opening: Vertical Cylinder (Dia: 0.35' x H: 0.35')
CIE Type: Direct

Input Watts (W): 11.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P759972

CATALOG NUMBER: LD6D10D010-EU6DR150210IC9035-6LBDP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P759972

CATALOG NUMBER: LD6D10D010-EU6DR150210IC9035-6LBDP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						100													
1	116	114	112	111	113	112	110	109	108	107	106	104	103	103	101	100	100	98						98													
2	113	110	107	105	111	108	106	104	105	103	102	102	101	100	100	98	98	96						96													
3	110	106	103	101	108	105	102	100	103	100	99	100	99	97	98	97	96	94						94													
4	108	103	100	98	106	102	99	97	100	98	96	99	97	95	97	95	94	93						93													
5	106	101	98	95	104	100	97	95	98	96	94	97	95	93	96	94	92	92						92													
6	104	99	95	93	102	98	95	93	97	94	92	96	93	92	95	93	91	90						90													
7	102	97	94	91	101	96	93	91	95	93	91	94	92	90	93	91	90	89						89													
8	100	95	92	90	99	95	92	90	94	91	89	93	91	89	92	90	89	88						88													
9	99	93	90	88	98	93	90	88	92	90	88	92	89	88	91	89	88	87						87													
10	97	92	89	87	96	92	89	87	91	89	87	91	88	87	90	88	86	86						86													

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1645413	1645413	1645413
5°	966918	954407	961948
10°	288582	290606	295048
15°	71778	73177	70919
20°	21478	24874	21937
25°	7572	9644	7665
30°	2778	3662	2831
35°	1394	1576	1351
40°	881	966	881
45°	651	693	651
50°	515	515	515
55°	432	432	432
60°	351	351	351
65°	264	264	264
70°	227	227	227
75°	144	144	189
80°	95	95	95
85°	50	50	50

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°

Vertical Angle: 45°

Luminance: 693 cd/sqm



TEST NUMBER: P759972

CATALOG NUMBER: LD6D10D010-EU6DR150210IC9035-6LBDP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	696.1	64.9
10°-20°	286.3	26.7
20°-30°	56.9	5.3
30°-40°	14.2	1.3
40°-50°	7.4	0.7
50°-60°	5.5	0.5
60°-70°	3.9	0.4
70°-80°	2.2	0.2
80°-90°	0.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1039.3	96.8
0°-40°	1053.5	98.2
0°-60°	1066.5	99.4
0°-90°	1073.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1073.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	14623	14623	14623	14623	14623	
5°	9514	9416	9391	9456	9465	695
15°	826	842	842	828	816	283
25°	97	110	124	110	98	51
35°	19	20	22	20	19	13
45°	9	9	10	9	9	7
55°	6	6	6	6	6	6
65°	4	4	4	4	4	4
75°	2	2	2	2	2	2
85°	1	1	1	1	1	1
90°	0	0	0	0	0	



TEST NUMBER: P759972

CATALOG NUMBER: LD6D10D010-EU6DR150210IC9035-6LBDP1MW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	14623.3	14623.3	14623.3	14623.3	14623.3
2.5°	13190.8	13201.9	13206.3	13219.3	13267.6
5°	9514.2	9416.4	9391.1	9456.1	9465.3
7.5°	5635.9	5655.7	5728.1	5744.2	5686.0
10°	3092.8	3118.2	3114.5	3136.7	3162.1
12.5°	1581.7	1561.9	1555.7	1581.1	1545.8
15°	826.4	841.9	842.5	827.7	816.5
17.5°	444.5	462.4	492.1	468.0	430.9
20°	262.5	278.6	304.0	284.1	268.1
22.5°	162.2	175.2	193.1	177.7	164.7
25°	97.2	110.2	123.8	109.6	98.4
27.5°	57.6	68.7	77.4	68.1	57.0
30°	37.1	43.3	48.9	42.7	37.8
32.5°	26.0	28.5	31.0	28.5	26.0
35°	19.2	20.4	21.7	20.4	18.6
37.5°	14.9	16.1	16.7	15.5	14.2
40°	12.4	13.0	13.6	13.0	12.4
42.5°	10.5	11.1	11.1	11.1	10.5
45°	9.3	9.3	9.9	9.3	9.3
47.5°	8.0	8.0	8.7	8.0	8.0
50°	7.4	7.4	7.4	7.4	7.4
52.5°	6.8	6.8	6.8	6.8	6.8
55°	6.2	6.2	6.2	6.2	6.2
57.5°	5.6	5.6	5.6	5.6	5.6
60°	5.0	5.0	5.0	5.0	5.0
62.5°	4.3	4.3	4.3	4.3	4.3
65°	3.7	3.7	3.7	3.7	3.7
67.5°	3.7	3.7	3.7	3.7	3.7
70°	3.1	3.1	3.1	3.1	3.1
72.5°	2.5	2.5	2.5	2.5	2.5
75°	1.9	1.9	1.9	1.9	2.5
77.5°	1.9	1.9	1.9	1.9	1.9
80°	1.2	1.2	1.2	1.2	1.2
82.5°	1.2	1.2	1.2	1.2	1.2
85°	0.6	0.6	0.6	0.6	0.6
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - - 90°-270°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)