

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P757972

Luminaire Tested: LD6D05D010-EU6DR150210IC9050-6LBS1H

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P757972  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-21)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD6D05D010-EU6DR150210IC9050-6LBS1H  
Description: 6 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 15° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 753.1 lumens  
Efficiency: N/A  
Efficacy: 100.4 lumens/watt  
Spacing Criteria (0/90/45): 0.22 / 0.22 / 0.23  
Luminous Opening: Vertical Cylinder (Dia: 0.35' x H: 0.35')  
CIE Type: Direct

Input Watts (W): 7.5  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight



TEST NUMBER: P757972  
CATALOG NUMBER: LD6D05D010-EU6DR150210IC9050-6LBS1H

### Luminous Intensity Polar Plot





TEST NUMBER: P757972

CATALOG NUMBER: LD6D05D010-EU6DR150210IC9050-6LBS1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						100													
1	116	114	112	111	113	112	110	109	108	107	106	104	103	103	101	100	100	98						98													
2	113	110	107	105	111	108	106	104	105	103	102	102	101	100	100	98	98	96						96													
3	110	106	103	101	108	105	102	100	103	100	99	100	99	97	98	97	96	94						94													
4	108	103	100	98	106	102	99	97	100	98	96	99	97	95	97	95	94	93						93													
5	106	101	98	95	104	100	97	95	98	96	94	97	95	93	96	94	92	92						92													
6	104	99	95	93	102	98	95	93	97	94	92	96	93	92	95	93	91	90						90													
7	102	97	94	91	101	96	93	91	95	93	91	94	92	90	93	91	90	89						89													
8	100	95	92	90	99	95	92	90	94	91	89	93	91	89	92	90	89	88						88													
9	99	93	90	88	98	93	90	88	92	90	88	92	89	88	91	89	88	87						87													
10	97	92	89	87	96	92	89	87	91	89	87	91	88	87	90	88	86	86						86													

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	1154623	1154623	1154623
5°	678515	669724	675029
10°	202505	203924	207040
15°	50368	51350	49769
20°	15072	17453	15391
25°	5313	6770	5383
30°	1954	2568	1984
35°	980	1104	944
40°	618	682	618
45°	455	490	455
50°	362	362	362
55°	299	299	299
60°	246	246	246
65°	186	186	186
70°	161	161	161
75°	98	98	128
80°	71	71	71
85°	33	33	33

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 45°

Vertical Angle: 45°

Luminance: 490 cd/sqm



TEST NUMBER: P757972

CATALOG NUMBER: LD6D05D010-EU6DR150210IC9050-6LBS1H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	488.5	64.9
10°-20°	200.9	26.7
20°-30°	39.9	5.3
30°-40°	10.0	1.3
40°-50°	5.2	0.7
50°-60°	3.9	0.5
60°-70°	2.7	0.4
70°-80°	1.6	0.2
80°-90°	0.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	729.3	96.8
0°-40°	739.3	98.2
0°-60°	748.4	99.4
0°-90°	753.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	753.1	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	10262	10262	10262	10262	10262	
5°	6676	6608	6590	6636	6642	488
15°	580	591	591	581	573	199
25°	68	77	87	77	69	36
35°	14	14	15	14	13	9
45°	6	6	7	6	6	5
55°	4	4	4	4	4	4
65°	3	3	3	3	3	3
75°	1	1	1	1	2	2
85°	0	0	0	0	0	0
90°	0	0	0	0	0	



TEST NUMBER: P757972

CATALOG NUMBER: LD6D05D010-EU6DR150210IC9050-6LBS1H

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	10261.5	10261.5	10261.5	10261.5	10261.5
2.5°	9256.3	9264.1	9267.2	9276.3	9310.2
5°	6676.4	6607.8	6589.9	6635.6	6642.1
7.5°	3954.8	3968.7	4019.6	4030.9	3990.0
10°	2170.3	2188.1	2185.5	2201.1	2218.9
12.5°	1109.9	1096.0	1091.7	1109.5	1084.7
15°	579.9	590.8	591.2	580.8	573.0
17.5°	311.9	324.5	345.4	328.4	302.3
20°	184.2	195.5	213.3	199.4	188.1
22.5°	113.8	122.9	135.5	124.7	115.6
25°	68.2	77.3	86.9	76.9	69.1
27.5°	40.4	48.2	54.3	47.8	40.0
30°	26.1	30.4	34.3	30.0	26.5
32.5°	18.2	20.0	21.7	20.0	18.2
35°	13.5	14.3	15.2	14.3	13.0
37.5°	10.4	11.3	11.7	10.9	10.0
40°	8.7	9.1	9.6	9.1	8.7
42.5°	7.4	7.8	7.8	7.8	7.4
45°	6.5	6.5	7.0	6.5	6.5
47.5°	5.6	5.6	6.1	5.6	5.6
50°	5.2	5.2	5.2	5.2	5.2
52.5°	4.8	4.8	4.8	4.8	4.8
55°	4.3	4.3	4.3	4.3	4.3
57.5°	3.9	3.9	3.9	3.9	3.9
60°	3.5	3.5	3.5	3.5	3.5
62.5°	3.0	3.0	3.0	3.0	3.0
65°	2.6	2.6	2.6	2.6	2.6
67.5°	2.6	2.6	2.6	2.6	2.6
70°	2.2	2.2	2.2	2.2	2.2
72.5°	1.7	1.7	1.7	1.7	1.7
75°	1.3	1.3	1.3	1.3	1.7
77.5°	1.3	1.3	1.3	1.3	1.3
80°	0.9	0.9	0.9	0.9	0.9
82.5°	0.9	0.9	0.9	0.9	0.9
85°	0.4	0.4	0.4	0.4	0.4
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report







— 0°-180°    - - 45°-225°    - - - - 90°-270°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)