

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P760830

Luminaire Tested: LD6D10D010-EU6DR700210IC9035-6LBDP1MW

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P760830  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD6D10D010-EU6DR700210IC9035-6LBDP1MW  
Description: 6 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 70° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 865.2 lumens  
Efficiency: N/A  
Efficacy: 73.9 lumens/watt  
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 11.7  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight



TEST NUMBER: P760830

CATALOG NUMBER: LD6D10D010-EU6DR700210IC9035-6LBDP1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P760830  
 CATALOG NUMBER: LD6D10D010-EU6DR700210IC9035-6LBDP1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	106267
5°	103108
10°	100240
15°	98919
20°	92379
25°	69392
30°	49052
35°	17380
40°	9143
45°	9735
50°	10080
55°	10267
60°	10336
65°	10109
70°	9552
75°	8865
80°	7865
85°	6393

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 60°  
 Luminance: 10336 cd/sqm



TEST NUMBER: P760830

CATALOG NUMBER: LD6D10D010-EU6DR700210IC9035-6LBDP1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	88.7	10.2
10°-20°	243.2	28.1
20°-30°	267.9	31.0
30°-40°	102.4	11.8
40°-50°	48.3	5.6
50°-60°	48.1	5.6
60°-70°	38.5	4.4
70°-80°	22.1	2.6
80°-90°	6.0	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	599.8	69.3
0°-40°	702.1	81.2
0°-60°	798.5	92.3
0°-90°	865.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	865.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	973	
5°	940	89
15°	874	243
25°	576	268
35°	130	102
45°	63	48
55°	54	48
65°	39	38
75°	21	22
85°	5	6
90°	0	



TEST NUMBER: P760830

CATALOG NUMBER: LD6D10D010-EU6DR700210IC9035-6LBDP1MW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	972.6
2.5°	962.4
5°	940.1
7.5°	921.5
10°	903.5
12.5°	888.2
15°	874.5
17.5°	841.4
20°	794.5
22.5°	693.1
25°	575.6
27.5°	501.1
30°	388.8
32.5°	251.2
35°	130.3
37.5°	70.4
40°	64.1
42.5°	63.6
45°	63.0
47.5°	61.6
50°	59.3
52.5°	56.7
55°	53.9
57.5°	50.8
60°	47.3
62.5°	43.3
65°	39.1
67.5°	34.5
70°	29.9
72.5°	25.3
75°	21.0
77.5°	16.5
80°	12.5
82.5°	8.8
85°	5.1
87.5°	2.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)