

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P758670

Luminaire Tested: LD6D05D010-EU6DR600210IC9050-6LBDP1H

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P758670  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD6D05D010-EU6DR600210IC9050-6LBDP1H  
Description: 6 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 60° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 710.4 lumens  
Efficiency: N/A  
Efficacy: 94.7 lumens/watt  
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.84  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 7.5  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight



TEST NUMBER: P758670

CATALOG NUMBER: LD6D05D010-EU6DR600210IC9050-6LBDP1H

### Luminous Intensity Polar Plot





TEST NUMBER: P758670

CATALOG NUMBER: LD6D05D010-EU6DR600210IC9050-6LBDP1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93																			
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86																			
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80																			
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70																			
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66																			
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62																			
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59																			
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55																			
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	92183
5°	94455
10°	95602
15°	91069
20°	80298
25°	64943
30°	43930
35°	22021
40°	3566
45°	3492
50°	3570
55°	3619
60°	3715
65°	3800
70°	3897
75°	3926
80°	3775
85°	3134

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 75°  
 Luminance: 3926 cd/sqm



TEST NUMBER: P758670

CATALOG NUMBER: LD6D05D010-EU6DR600210IC9050-6LBDP1H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	82.3	11.6
10°-20°	222.7	31.3
20°-30°	239.6	33.7
30°-40°	104.2	14.7
40°-50°	17.5	2.5
50°-60°	17.0	2.4
60°-70°	14.5	2.0
70°-80°	9.7	1.4
80°-90°	2.9	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	544.6	76.7
0°-40°	648.8	91.3
0°-60°	683.2	96.2
0°-90°	710.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	710.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	844	
5°	861	82
15°	805	223
25°	539	240
35°	165	104
45°	23	17
55°	19	17
65°	15	15
75°	9	10
85°	2	3
90°	0	



TEST NUMBER: P758670

CATALOG NUMBER: LD6D05D010-EU6DR600210IC9050-6LBDP1H

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	843.7
2.5°	867.4
5°	861.2
7.5°	863.2
10°	861.7
12.5°	843.8
15°	805.1
17.5°	753.0
20°	690.6
22.5°	623.7
25°	538.7
27.5°	430.9
30°	348.2
32.5°	268.4
35°	165.1
37.5°	70.6
40°	25.0
42.5°	23.0
45°	22.6
47.5°	21.8
50°	21.0
52.5°	20.0
55°	19.0
57.5°	18.0
60°	17.0
62.5°	15.9
65°	14.7
67.5°	13.5
70°	12.2
72.5°	10.8
75°	9.3
77.5°	7.7
80°	6.0
82.5°	4.3
85°	2.5
87.5°	0.9
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)