

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P758827

Luminaire Tested: LD6D05D010-EU6DR700210IC9050-6LBDP1LI

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P758827
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D05D010-EU6DR700210IC9050-6LBDP1LI
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 750.9 lumens
Efficiency: N/A
Efficacy: 100.1 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 7.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P758827

CATALOG NUMBER: LD6D05D010-EU6DR700210IC9050-6LBDP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P758827

CATALOG NUMBER: LD6D05D010-EU6DR700210IC9050-6LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	92238
5°	89497
10°	87004
15°	85854
20°	80170
25°	60230
30°	42580
35°	15086
40°	7930
45°	8452
50°	8754
55°	8915
60°	8959
65°	8790
70°	8306
75°	7683
80°	6795
85°	5516

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 8968 cd/sqm



TEST NUMBER: P758827

CATALOG NUMBER: LD6D05D010-EU6DR700210IC9050-6LBDP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	77.0	10.2
10°-20°	211.1	28.1
20°-30°	232.5	31.0
30°-40°	88.8	11.8
40°-50°	42.0	5.6
50°-60°	41.7	5.6
60°-70°	33.4	4.5
70°-80°	19.2	2.6
80°-90°	5.2	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	520.6	69.3
0°-40°	609.4	81.2
0°-60°	693.1	92.3
0°-90°	750.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	750.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	844	
5°	816	77
15°	759	211
25°	500	233
35°	113	89
45°	55	42
55°	47	42
65°	34	33
75°	18	19
85°	4	5
90°	0	



TEST NUMBER: P758827

CATALOG NUMBER: LD6D05D010-EU6DR700210IC9050-6LBDP1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	844.2
2.5°	835.4
5°	816.0
7.5°	799.8
10°	784.2
12.5°	771.0
15°	759.0
17.5°	730.3
20°	689.5
22.5°	601.6
25°	499.6
27.5°	434.9
30°	337.5
32.5°	218.0
35°	113.1
37.5°	61.1
40°	55.6
42.5°	55.2
45°	54.7
47.5°	53.5
50°	51.5
52.5°	49.2
55°	46.8
57.5°	44.1
60°	41.0
62.5°	37.6
65°	34.0
67.5°	30.0
70°	26.0
72.5°	21.9
75°	18.2
77.5°	14.3
80°	10.8
82.5°	7.6
85°	4.4
87.5°	1.7
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)