

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P767857

Luminaire Tested: LD6D55D010-EU6DR2555659024-6LBDP1MW

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P767857  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-4)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD6D55D010-EU6DR2555659024-6LBDP1MW  
Description: 6 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 25° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4414.6 lumens  
Efficiency: N/A  
Efficacy: 75.9 lumens/watt  
Spacing Criteria (0/90/45): 0.42 / 0.42 / 0.45  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 58.2  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight

TEST NUMBER: P767857

CATALOG NUMBER: LD6D55D010-EU6DR2555659024-6LBDP1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P767857

CATALOG NUMBER: LD6D55D010-EU6DR2555659024-6LBDP1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						100													
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96						96													
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92						92													
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89						89													
4	103	97	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85						85													
5	100	93	89	86	98	93	89	86	91	87	85	89	86	84	88	85	83	82						82													
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79						79													
7	93	87	82	79	92	86	82	79	85	81	78	84	80	78	83	80	78	77						77													
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74						74													
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	72						72													
10	85	78	74	71	85	78	74	71	77	73	71	76	73	71	76	73	70	69						69													

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1829429
5°	1703882
10°	1215428
15°	715837
20°	445406
25°	244439
30°	111793
35°	42336
40°	19169
45°	11527
50°	4793
55°	3086
60°	2163
65°	1448
70°	224
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 11527 cd/sqm



TEST NUMBER: P767857

CATALOG NUMBER: LD6D55D010-EU6DR2555659024-6LBDP1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	1335.1	30.2
10°-20°	1808.3	41.0
20°-30°	956.9	21.7
30°-40°	236.2	5.4
40°-50°	57.6	1.3
50°-60°	15.2	0.3
60°-70°	5.1	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4100.4	92.9
0°-40°	4336.6	98.2
0°-60°	4409.5	99.9
0°-90°	4414.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4414.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	16744	
5°	15535	###
15°	6328	1808
25°	2028	957
35°	317	236
45°	75	58
55°	16	15
65°	6	5
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P767857

CATALOG NUMBER: LD6D55D010-EU6DR2555659024-6LBDP1MW

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	16743.7
2.5°	16468.5
5°	15535.3
7.5°	13660.4
10°	10955.1
12.5°	8281.4
15°	6328.4
17.5°	4932.1
20°	3830.7
22.5°	2872.8
25°	2027.6
27.5°	1359.7
30°	886.1
32.5°	539.1
35°	317.4
37.5°	194.2
40°	134.4
42.5°	102.8
45°	74.6
47.5°	45.0
50°	28.2
52.5°	20.4
55°	16.2
57.5°	12.7
60°	9.9
62.5°	7.7
65°	5.6
67.5°	2.1
70°	0.7
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)