

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P760220

Luminaire Tested: LD6D10D010-EU6DR300210IC9040-6LBS1B

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P760220
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D10D010-EU6DR300210IC9040-6LBS1B
Description: 6 INCH ROUND SHALLOW SPECULAR BLACK TRIM, WITH 30° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1086.7 lumens
Efficiency: N/A
Efficacy: 92.9 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.49
Luminous Opening: Rectangular (W 0.38' x L: 0.38' x H: 0')
CIE Type: Direct

Input Watts (W): 11.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P760220
CATALOG NUMBER: LD6D10D010-EU6DR300210IC9040-6LBS1B

Luminous Intensity Polar Plot





TEST NUMBER: P760220

CATALOG NUMBER: LD6D10D010-EU6DR300210IC9040-6LBS1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96																			
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92																			
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89																			
4	103	98	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85																			
5	100	94	89	86	98	93	89	86	91	88	85	90	86	84	88	86	83	82																			
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79																			
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77																			
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74																			
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	72																			
10	85	78	74	71	85	78	74	71	77	73	71	76	73	71	76	73	70	69																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	267458	267458	267458
5°	259782	259474	259797
10°	225004	223426	224957
15°	146807	146022	145285
20°	73001	75738	72903
25°	36772	41468	36021
30°	14725	16042	12825
35°	6831	6541	5485
40°	2948	3277	2778
45°	2078	2576	2100
50°	714	1881	762
55°	414	774	440
60°	291	337	291
65°	181	181	181
70°	112	67	112
75°	0	59	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°
 Vertical Angle: 45°
 Luminance: 2576 cd/sqm



TEST NUMBER: P760220
 CATALOG NUMBER: LD6D10D010-EU6DR300210IC9040-6LBS1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	307.3	28.3
10°-20°	494.8	45.5
20°-30°	213.8	19.7
30°-40°	48.7	4.5
40°-50°	16.7	1.5
50°-60°	4.1	0.4
60°-70°	1.1	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1016.0	93.5
0°-40°	1064.7	98.0
0°-60°	1085.5	99.9
0°-90°	1086.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1086.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3494	3494	3494	3494	3494	
5°	3381	3378	3377	3384	3381	308
15°	1853	1830	1843	1837	1833	496
25°	435	452	491	440	426	208
35°	73	75	70	70	59	50
45°	19	24	24	24	19	14
55°	3	3	6	3	3	3
65°	1	1	1	1	1	1
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	



TEST NUMBER: P760220

CATALOG NUMBER: LD6D10D010-EU6DR300210IC9040-6LBS1B

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3494.2	3494.2	3494.2	3494.2	3494.2
2.5°	3471.1	3468.6	3470.0	3471.7	3472.4
5°	3381.0	3377.7	3377.0	3384.1	3381.2
7.5°	3199.3	3194.7	3187.6	3203.6	3218.5
10°	2894.9	2889.8	2874.6	2882.1	2894.3
12.5°	2445.7	2429.0	2428.7	2452.7	2449.4
15°	1852.6	1830.3	1842.7	1836.7	1833.4
17.5°	1245.8	1237.2	1253.7	1248.7	1227.3
20°	896.2	898.4	929.8	914.0	895.0
22.5°	654.0	662.0	699.2	658.6	643.7
25°	435.4	451.9	491.0	440.4	426.5
27.5°	267.8	275.4	315.0	264.4	256.8
30°	166.6	162.8	181.5	155.8	145.1
32.5°	109.3	104.4	110.5	99.2	90.6
35°	73.1	74.6	70.0	69.5	58.7
37.5°	45.6	52.5	46.3	49.4	37.8
40°	29.5	38.1	32.8	36.2	27.8
42.5°	24.2	29.3	26.9	28.6	24.7
45°	19.2	23.8	23.8	23.8	19.4
47.5°	10.7	15.9	20.4	16.3	11.3
50°	6.0	8.1	15.8	8.4	6.4
52.5°	4.1	4.6	10.8	4.8	4.3
55°	3.1	3.3	5.8	3.4	3.3
57.5°	2.4	2.6	3.1	2.6	2.4
60°	1.9	1.9	2.2	2.1	1.9
62.5°	1.4	1.4	1.5	1.4	1.4
65°	1.0	1.0	1.0	1.0	1.0
67.5°	0.5	0.7	0.7	0.7	0.7
70°	0.5	0.3	0.3	0.3	0.5
72.5°	0.3	0.2	0.2	0.2	0.2
75°	0.0	0.0	0.2	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - - 90°-270°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)