

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P760684

Luminaire Tested: LD6D10D010-EU6DR600210IC9040-6LBDP1B

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P760684  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD6D10D010-EU6DR600210IC9040-6LBDP1B  
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 60° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 890.4 lumens  
Efficiency: N/A  
Efficacy: 76.1 lumens/watt  
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 11.7  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight



TEST NUMBER: P760684

CATALOG NUMBER: LD6D10D010-EU6DR600210IC9040-6LBDP1B

### Luminous Intensity Polar Plot





TEST NUMBER: P760684

CATALOG NUMBER: LD6D10D010-EU6DR600210IC9040-6LBDP1B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93																			
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86																			
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80																			
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70																			
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66																			
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62																			
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59																			
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55																			
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	115543
5°	118387
10°	119811
15°	114133
20°	100634
25°	81399
30°	55058
35°	27584
40°	4479
45°	4388
50°	4470
55°	4534
60°	4655
65°	4757
70°	4888
75°	4939
80°	4782
85°	4012

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 75°  
 Luminance: 4939 cd/sqm



TEST NUMBER: P760684

CATALOG NUMBER: LD6D10D010-EU6DR600210IC9040-6LBDP1B

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	103.2	11.6
10°-20°	279.1	31.3
20°-30°	300.3	33.7
30°-40°	130.5	14.7
40°-50°	21.9	2.5
50°-60°	21.3	2.4
60°-70°	18.2	2.0
70°-80°	12.2	1.4
80°-90°	3.7	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	682.6	76.7
0°-40°	813.1	91.3
0°-60°	856.3	96.2
0°-90°	890.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	890.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1058	
5°	1079	103
15°	1009	279
25°	675	300
35°	207	131
45°	28	22
55°	24	21
65°	18	18
75°	12	12
85°	3	4
90°	0	



TEST NUMBER: P760684

CATALOG NUMBER: LD6D10D010-EU6DR600210IC9040-6LBDP1B

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1057.5
2.5°	1087.2
5°	1079.4
7.5°	1081.8
10°	1079.9
12.5°	1057.6
15°	1009.0
17.5°	943.8
20°	865.5
22.5°	781.7
25°	675.2
27.5°	540.0
30°	436.4
32.5°	336.3
35°	206.8
37.5°	88.5
40°	31.4
42.5°	28.9
45°	28.4
47.5°	27.4
50°	26.3
52.5°	25.0
55°	23.8
57.5°	22.6
60°	21.3
62.5°	19.9
65°	18.4
67.5°	16.9
70°	15.3
72.5°	13.5
75°	11.7
77.5°	9.6
80°	7.6
82.5°	5.4
85°	3.2
87.5°	1.1
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)