

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P768481

Luminaire Tested: LD6D55D010-EU6DR6555659024-6LBDP1MW

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P768481  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD6D55D010-EU6DR6555659024-6LBDP1MW  
Description: 6 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 65° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4218.1 lumens  
Efficiency: N/A  
Efficacy: 72.5 lumens/watt  
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 58.2  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight

TEST NUMBER: P768481

CATALOG NUMBER: LD6D55D010-EU6DR6555659024-6LBDP1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P768481

CATALOG NUMBER: LD6D55D010-EU6DR6555659024-6LBDP1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93																			
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87																			
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80																			
4	97	89	84	79	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	83	78	73	90	83	77	73	81	76	72	79	75	72	77	74	71	69																			
6	87	78	72	68	86	77	72	68	76	71	67	74	70	67	73	69	66	65																			
7	83	73	67	63	81	73	67	63	71	66	62	70	66	62	69	65	62	60																			
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	57																			
9	75	65	59	55	74	65	59	55	64	58	55	63	58	55	62	58	54	53																			
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	453760
5°	454133
10°	470124
15°	470898
20°	433535
25°	369395
30°	282783
35°	199781
40°	117926
45°	47870
50°	17355
55°	9677
60°	5550
65°	3051
70°	3195
75°	2491
80°	2580
85°	2257

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 47870 cd/sqm



TEST NUMBER: P768481

CATALOG NUMBER: LD6D55D010-EU6DR6555659024-6LBDP1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	399.9	9.5
10°-20°	1153.5	27.3
20°-30°	1384.0	32.8
30°-40°	930.1	22.0
40°-50°	278.4	6.6
50°-60°	49.1	1.2
60°-70°	14.0	0.3
70°-80°	6.8	0.2
80°-90°	2.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2937.4	69.6
0°-40°	3867.5	91.7
0°-60°	4195.1	99.5
0°-90°	4218.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4218.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4153	
5°	4141	400
15°	4163	1154
25°	3064	1384
35°	1498	930
45°	310	278
55°	51	49
65°	12	14
75°	6	7
85°	2	2
90°	0	



TEST NUMBER: P768481

CATALOG NUMBER: LD6D55D010-EU6DR6555659024-6LBDP1MW

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	4153.0
2.5°	4170.7
5°	4140.6
7.5°	4203.1
10°	4237.4
12.5°	4229.1
15°	4163.0
17.5°	4001.3
20°	3728.6
22.5°	3407.6
25°	3064.1
27.5°	2676.4
30°	2241.4
32.5°	1847.2
35°	1497.8
37.5°	1152.6
40°	826.8
42.5°	540.0
45°	309.8
47.5°	164.1
50°	102.1
52.5°	70.8
55°	50.8
57.5°	36.6
60°	25.4
62.5°	16.5
65°	11.8
67.5°	10.6
70°	10.0
72.5°	7.7
75°	5.9
77.5°	5.3
80°	4.1
82.5°	3.0
85°	1.8
87.5°	1.2
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)