

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P768414

Luminaire Tested: LD6D55D010-EU6DR6055659027-6LBDP1H

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P768414
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D55D010-EU6DR6055659027-6LBDP1H
Description: 6 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6338.0 lumens
Efficiency: N/A
Efficacy: 108.9 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 58.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P768414

CATALOG NUMBER: LD6D55D010-EU6DR6055659027-6LBDP1H

Luminous Intensity Polar Plot





TEST NUMBER: P768414

CATALOG NUMBER: LD6D55D010-EU6DR6055659027-6LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100															
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93				93															
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86				86															
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80				80															
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75				75															
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70				70															
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66				66															
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62				62															
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59				59															
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55				55															
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53				53															

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	822428
5°	842657
10°	852833
15°	812438
20°	716322
25°	579380
30°	391902
35°	196379
40°	31849
45°	31182
50°	31803
55°	32288
60°	33172
65°	33945
70°	34725
75°	35165
80°	33914
85°	28207

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 35165 cd/sqm



TEST NUMBER: P768414

CATALOG NUMBER: LD6D55D010-EU6DR6055659027-6LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	734.3	11.6
10°-20°	1986.7	31.3
20°-30°	2137.5	33.7
30°-40°	929.1	14.7
40°-50°	156.0	2.5
50°-60°	151.8	2.4
60°-70°	129.8	2.0
70°-80°	86.9	1.4
80°-90°	26.0	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4858.5	76.7
0°-40°	5787.6	91.3
0°-60°	6095.4	96.2
0°-90°	6338.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6338.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7527	
5°	7683	734
15°	7182	1987
25°	4806	2138
35°	1472	929
45°	202	156
55°	170	152
65°	131	130
75°	83	87
85°	22	26
90°	0	



TEST NUMBER: P768414

CATALOG NUMBER: LD6D55D010-EU6DR6055659027-6LBDP1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	7527.2
2.5°	7738.8
5°	7683.0
7.5°	7700.6
10°	7686.9
12.5°	7528.2
15°	7182.4
17.5°	6718.1
20°	6160.7
22.5°	5564.1
25°	4805.9
27.5°	3843.9
30°	3106.3
32.5°	2394.1
35°	1472.3
37.5°	629.9
40°	223.3
42.5°	205.7
45°	201.8
47.5°	194.9
50°	187.1
52.5°	178.3
55°	169.5
57.5°	160.7
60°	151.8
62.5°	142.0
65°	131.3
67.5°	120.5
70°	108.7
72.5°	96.0
75°	83.3
77.5°	68.6
80°	53.9
82.5°	38.2
85°	22.5
87.5°	7.8
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)