

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P768498

Luminaire Tested: LD6D55D010-EU6DR6555659027-6LBS1MW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P768498
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D55D010-EU6DR6555659027-6LBS1MW
Description: 6 INCH ROUND SHALLOW MATTE WHITE TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5539.3 lumens
Efficiency: N/A
Efficacy: 95.2 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct


Input Watts (W): 58.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P768498
CATALOG NUMBER: LD6D55D010-EU6DR6555659027-6LBS1MW

Luminous Intensity Polar Plot





TEST NUMBER: P768498
 CATALOG NUMBER: LD6D55D010-EU6DR6555659027-6LBS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10		0		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93			
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85			
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78			
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72			
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66			
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61			
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56			
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52			
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49			
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	293742
5°	293000
10°	292752
15°	283728
20°	258298
25°	225094
30°	187211
35°	148335
40°	107065
45°	67637
50°	35254
55°	18736
60°	9847
65°	5417
70°	2271
75°	2505
80°	1749
85°	1474

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 67637 cd/sqm



TEST NUMBER: P768498

CATALOG NUMBER: LD6D55D010-EU6DR6555659027-6LBS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	475.6	8.6
10°-20°	1302.5	23.5
20°-30°	1592.1	28.7
30°-40°	1291.7	23.3
40°-50°	643.7	11.6
50°-60°	179.6	3.2
60°-70°	40.8	0.7
70°-80°	10.6	0.2
80°-90°	2.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3370.2	60.8
0°-40°	4661.9	84.2
0°-60°	5485.2	99.0
0°-90°	5539.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5539.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5030	
5°	4998	476
15°	4692	1302
25°	3493	1592
35°	2080	1292
45°	819	644
55°	184	180
65°	39	41
75°	11	11
85°	2	3
90°	0	



TEST NUMBER: P768498

CATALOG NUMBER: LD6D55D010-EU6DR6555659027-6LBS1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	5029.5
2.5°	5025.8
5°	4997.7
7.5°	4981.5
10°	4936.4
12.5°	4844.8
15°	4692.5
17.5°	4454.5
20°	4155.9
22.5°	3833.7
25°	3493.0
27.5°	3128.6
30°	2776.0
32.5°	2427.9
35°	2080.5
37.5°	1733.9
40°	1404.3
42.5°	1095.3
45°	818.9
47.5°	570.6
50°	388.0
52.5°	267.6
55°	184.0
57.5°	124.2
60°	84.3
62.5°	58.4
65°	39.2
67.5°	20.0
70°	13.3
72.5°	12.6
75°	11.1
77.5°	7.4
80°	5.2
82.5°	3.7
85°	2.2
87.5°	1.5
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)