

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P760855

Luminaire Tested: LD6D10D010-EU6DR700210IC9050-6LBDP1LI

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P760855
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D10D010-EU6DR700210IC9050-6LBDP1LI
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1181.0 lumens
Efficiency: N/A
Efficacy: 100.9 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 11.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P760855

CATALOG NUMBER: LD6D10D010-EU6DR700210IC9050-6LBDP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P760855

CATALOG NUMBER: LD6D10D010-EU6DR700210IC9050-6LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	145076
5°	140761
10°	136830
15°	135048
20°	126098
25°	94733
30°	66968
35°	23715
40°	12466
45°	13289
50°	13768
55°	14020
60°	14095
65°	13806
70°	13034
75°	12074
80°	10697
85°	8650

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 14113 cd/sqm



TEST NUMBER: P760855

CATALOG NUMBER: LD6D10D010-EU6DR700210IC9050-6LBDP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	121.1	10.3
10°-20°	332.0	28.1
20°-30°	365.7	31.0
30°-40°	139.7	11.8
40°-50°	66.0	5.6
50°-60°	65.6	5.6
60°-70°	52.5	4.4
70°-80°	30.2	2.6
80°-90°	8.2	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	818.8	69.3
0°-40°	958.5	81.2
0°-60°	1090.1	92.3
0°-90°	1181.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1181.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1328	
5°	1283	121
15°	1194	332
25°	786	366
35°	178	140
45°	86	66
55°	74	66
65°	53	53
75°	29	30
85°	7	8
90°	0	



TEST NUMBER: P760855

CATALOG NUMBER: LD6D10D010-EU6DR700210IC9050-6LBDP1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	1327.8
2.5°	1313.9
5°	1283.4
7.5°	1258.0
10°	1233.3
12.5°	1212.5
15°	1193.9
17.5°	1148.7
20°	1084.5
22.5°	946.2
25°	785.8
27.5°	684.0
30°	530.8
32.5°	342.9
35°	177.8
37.5°	96.1
40°	87.4
42.5°	86.8
45°	86.0
47.5°	84.1
50°	81.0
52.5°	77.3
55°	73.6
57.5°	69.4
60°	64.5
62.5°	59.1
65°	53.4
67.5°	47.1
70°	40.8
72.5°	34.5
75°	28.6
77.5°	22.5
80°	17.0
82.5°	12.0
85°	6.9
87.5°	2.8
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)