

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P757129

Luminaire Tested: LD6D02D010-EU6DR300210IC9024-6LBS1MW

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P757129  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-16)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD6D02D010-EU6DR300210IC9024-6LBS1MW  
Description: 6 INCH ROUND SHALLOW MATTE WHITE TRIM, WITH 30° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 309.0 lumens  
Efficiency: N/A  
Efficacy: 60.6 lumens/watt  
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.49  
Luminous Opening: Rectangular (W 0.38' x L: 0.38' x H: 0')  
CIE Type: Direct

Input Watts (W): 5.1  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight



TEST NUMBER: P757129

CATALOG NUMBER: LD6D02D010-EU6DR300210IC9024-6LBS1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P757129

CATALOG NUMBER: LD6D02D010-EU6DR300210IC9024-6LBS1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						100													
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96						96													
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92						92													
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89						89													
4	103	98	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85						85													
5	100	94	89	86	98	93	89	86	91	88	85	90	86	84	88	86	83	82						82													
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79						79													
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77						77													
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74						74													
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	72						72													
10	85	78	74	71	85	78	74	71	77	73	71	76	73	71	76	73	70	69						69													

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	76046	76046	76046
5°	73862	73778	73870
10°	63975	63524	63959
15°	41746	41516	41310
20°	20755	21537	20722
25°	10456	11790	10236
30°	4189	4561	3650
35°	1944	1860	1560
40°	839	929	789
45°	585	736	595
50°	202	536	214
55°	120	227	120
60°	77	92	77
65°	54	54	54
70°	45	22	45
75°	0	30	0
80°	0	0	0
85°	0	0	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 22.5°

Vertical Angle: 45°

Luminance: 736 cd/sqm



TEST NUMBER: P757129

CATALOG NUMBER: LD6D02D010-EU6DR300210IC9024-6LBS1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	87.4	28.3
10°-20°	140.7	45.5
20°-30°	60.8	19.7
30°-40°	13.9	4.5
40°-50°	4.8	1.5
50°-60°	1.2	0.4
60°-70°	0.3	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	288.9	93.5
0°-40°	302.7	98.0
0°-60°	308.6	99.9
0°-90°	309.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	309.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	994	994	994	994	994	
5°	961	960	960	962	961	87
15°	527	520	524	522	521	141
25°	124	128	140	125	121	59
35°	21	21	20	20	17	14
45°	5	7	7	7	6	4
55°	1	1	2	1	1	1
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	



TEST NUMBER: P757129

CATALOG NUMBER: LD6D02D010-EU6DR300210IC9024-6LBS1MW

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	993.5	993.5	993.5	993.5	993.5
2.5°	986.9	986.2	986.6	987.1	987.3
5°	961.3	960.4	960.2	962.2	961.4
7.5°	909.7	908.4	906.4	910.9	915.1
10°	823.1	821.7	817.3	819.4	822.9
12.5°	695.4	690.6	690.5	697.4	696.4
15°	526.8	520.4	523.9	522.2	521.3
17.5°	354.2	351.8	356.5	355.1	348.9
20°	254.8	255.4	264.4	259.9	254.4
22.5°	185.9	188.2	198.8	187.2	183.0
25°	123.8	128.5	139.6	125.2	121.2
27.5°	76.1	78.3	89.6	75.2	73.0
30°	47.4	46.3	51.6	44.3	41.3
32.5°	31.1	29.7	31.4	28.2	25.8
35°	20.8	21.2	19.9	19.8	16.7
37.5°	12.9	15.0	13.2	14.0	10.7
40°	8.4	10.8	9.3	10.3	7.9
42.5°	6.9	8.4	7.7	8.1	7.0
45°	5.4	6.8	6.8	6.8	5.5
47.5°	3.0	4.5	5.8	4.6	3.2
50°	1.7	2.3	4.5	2.4	1.8
52.5°	1.1	1.3	3.1	1.4	1.2
55°	0.9	0.9	1.7	1.0	0.9
57.5°	0.7	0.7	0.9	0.7	0.7
60°	0.5	0.5	0.6	0.6	0.5
62.5°	0.4	0.4	0.5	0.4	0.4
65°	0.3	0.3	0.3	0.3	0.3
67.5°	0.2	0.2	0.2	0.2	0.2
70°	0.2	0.1	0.1	0.1	0.2
72.5°	0.1	0.1	0.1	0.1	0.1
75°	0.0	0.0	0.1	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report







— 0°-180°    - - 45°-225°    - - - - 90°-270°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)