

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P768508

Luminaire Tested: LD6D55D010-EU6DR6555659030-6LBS1B

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P768508
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D55D010-EU6DR6555659030-6LBS1B
Description: 6 INCH ROUND SHALLOW SPECULAR BLACK TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5576.0 lumens
Efficiency: N/A
Efficacy: 95.8 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct


Input Watts (W): 58.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P768508
CATALOG NUMBER: LD6D55D010-EU6DR6555659030-6LBS1B

Luminous Intensity Polar Plot





TEST NUMBER: P768508
 CATALOG NUMBER: LD6D55D010-EU6DR6555659030-6LBS1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93																			
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85																			
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78																			
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72																			
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66																			
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61																			
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56																			
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52																			
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49																			
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	295687
5°	294946
10°	294692
15°	285608
20°	260013
25°	226583
30°	188451
35°	149319
40°	107774
45°	68084
50°	35490
55°	18868
60°	9905
65°	5445
70°	2288
75°	2527
80°	1749
85°	1474

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 68084 cd/sqm



TEST NUMBER: P768508

CATALOG NUMBER: LD6D55D010-EU6DR6555659030-6LBS1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	478.8	8.6
10°-20°	1311.1	23.5
20°-30°	1602.6	28.7
30°-40°	1300.3	23.3
40°-50°	648.0	11.6
50°-60°	180.7	3.2
60°-70°	41.1	0.7
70°-80°	10.7	0.2
80°-90°	2.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3392.5	60.8
0°-40°	4692.8	84.2
0°-60°	5521.5	99.0
0°-90°	5576.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5576.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5063	
5°	5031	479
15°	4724	1311
25°	3516	1603
35°	2094	1300
45°	824	648
55°	185	181
65°	39	41
75°	11	11
85°	2	3
90°	0	



TEST NUMBER: P768508

CATALOG NUMBER: LD6D55D010-EU6DR6555659030-6LBS1B

CANDELA DISTRIBUTION (FULL):

0°	
0°	5062.8
2.5°	5059.1
5°	5030.9
7.5°	5014.5
10°	4969.1
12.5°	4876.9
15°	4723.6
17.5°	4484.0
20°	4183.5
22.5°	3859.1
25°	3516.1
27.5°	3149.3
30°	2794.4
32.5°	2444.0
35°	2094.3
37.5°	1745.4
40°	1413.6
42.5°	1102.6
45°	824.3
47.5°	574.4
50°	390.6
52.5°	269.3
55°	185.3
57.5°	125.0
60°	84.8
62.5°	58.8
65°	39.4
67.5°	20.1
70°	13.4
72.5°	12.6
75°	11.2
77.5°	7.4
80°	5.2
82.5°	3.7
85°	2.2
87.5°	1.5
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)