

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P768453

Luminaire Tested: LD6D55D010-EU6DR6055659040-6LBDP1H

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P768453  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD6D55D010-EU6DR6055659040-6LBDP1H  
Description: 6 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 60° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6906.8 lumens  
Efficiency: N/A  
Efficacy: 118.7 lumens/watt  
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct


Input Watts (W): 58.2  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



Downlight

TEST NUMBER: P768453  
CATALOG NUMBER: LD6D55D010-EU6DR6055659040-6LBDP1H

### Luminous Intensity Polar Plot





TEST NUMBER: P768453

CATALOG NUMBER: LD6D55D010-EU6DR6055659040-6LBDP1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						100													
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93						93													
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86						86													
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80						80													
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75						75													
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70						70													
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66						66													
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62						62													
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59						59													
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55						55													
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53						53													

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	896233
5°	918280
10°	929364
15°	885352
20°	780610
25°	631375
30°	427076
35°	214013
40°	34716
45°	33979
50°	34659
55°	35184
60°	36165
65°	36970
70°	37856
75°	38289
80°	36934
85°	30839

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 75°  
 Luminance: 38289 cd/sqm



TEST NUMBER: P768453

CATALOG NUMBER: LD6D55D010-EU6DR6055659040-6LBDP1H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	800.2	11.6
10°-20°	2165.0	31.3
20°-30°	2329.3	33.7
30°-40°	1012.5	14.7
40°-50°	170.1	2.5
50°-60°	165.4	2.4
60°-70°	141.4	2.0
70°-80°	94.6	1.4
80°-90°	28.3	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5294.5	76.7
0°-40°	6307.1	91.3
0°-60°	6642.5	96.2
0°-90°	6906.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6906.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	8203	
5°	8372	800
15°	7827	2165
25°	5237	2329
35°	1604	1013
45°	220	170
55°	185	165
65°	143	141
75°	91	95
85°	25	28
90°	0	



TEST NUMBER: P768453

CATALOG NUMBER: LD6D55D010-EU6DR6055659040-6LBDP1H

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	8202.7
2.5°	8433.3
5°	8372.5
7.5°	8391.7
10°	8376.7
12.5°	8203.8
15°	7827.0
17.5°	7321.0
20°	6713.6
22.5°	6063.4
25°	5237.2
27.5°	4188.9
30°	3385.1
32.5°	2609.0
35°	1604.5
37.5°	686.4
40°	243.4
42.5°	224.2
45°	219.9
47.5°	212.4
50°	203.9
52.5°	194.3
55°	184.7
57.5°	175.1
60°	165.5
62.5°	154.8
65°	143.0
67.5°	131.3
70°	118.5
72.5°	104.6
75°	90.7
77.5°	74.7
80°	58.7
82.5°	41.6
85°	24.6
87.5°	8.5
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)