

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P768454

Luminaire Tested: LD6D55D010-EU6DR6055659040-6LBDP1LI

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P768454  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD6D55D010-EU6DR6055659040-6LBDP1LI  
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 60° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7252.2 lumens  
Efficiency: N/A  
Efficacy: 124.6 lumens/watt  
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct


Input Watts (W): 58.2  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



Downlight

TEST NUMBER: P768454  
CATALOG NUMBER: LD6D55D010-EU6DR6055659040-6LBDP1LI

### Luminous Intensity Polar Plot





TEST NUMBER: P768454

CATALOG NUMBER: LD6D55D010-EU6DR6055659040-6LBDP1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93																			
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86																			
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80																			
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70																			
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66																			
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62																			
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59																			
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55																			
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	941052
5°	964191
10°	975839
15°	929613
20°	819631
25°	662949
30°	448423
35°	224710
40°	36456
45°	35678
50°	36393
55°	36936
60°	37957
65°	38832
70°	39740
75°	40231
80°	38759
85°	32344

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 75°  
 Luminance: 40231 cd/sqm



TEST NUMBER: P768454

CATALOG NUMBER: LD6D55D010-EU6DR6055659040-6LBDP1LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	840.2	11.6
10°-20°	2273.2	31.3
20°-30°	2445.8	33.7
30°-40°	1063.1	14.7
40°-50°	178.6	2.5
50°-60°	173.6	2.4
60°-70°	148.5	2.0
70°-80°	99.4	1.4
80°-90°	29.7	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5559.2	76.7
0°-40°	6622.4	91.3
0°-60°	6974.6	96.2
0°-90°	7252.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7252.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	8613	
5°	8791	840
15°	8218	2273
25°	5499	2446
35°	1685	1063
45°	231	179
55°	194	174
65°	150	148
75°	95	99
85°	26	30
90°	0	



TEST NUMBER: P768454  
CATALOG NUMBER: LD6D55D010-EU6DR6055659040-6LBDP1LI

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	8612.9
2.5°	8855.0
5°	8791.1
7.5°	8811.3
10°	8795.6
12.5°	8614.0
15°	8218.3
17.5°	7687.0
20°	7049.2
22.5°	6366.6
25°	5499.1
27.5°	4398.3
30°	3554.3
32.5°	2739.4
35°	1684.7
37.5°	720.7
40°	255.6
42.5°	235.4
45°	230.9
47.5°	223.1
50°	214.1
52.5°	204.0
55°	193.9
57.5°	183.8
60°	173.7
62.5°	162.5
65°	150.2
67.5°	137.9
70°	124.4
72.5°	109.8
75°	95.3
77.5°	78.5
80°	61.6
82.5°	43.7
85°	25.8
87.5°	9.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)