

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P768533

Luminaire Tested: LD6D55D010-EU6DR6555659040-6LBDP1MW

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P768533
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D55D010-EU6DR6555659040-6LBDP1MW
Description: 6 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5207.0 lumens
Efficiency: N/A
Efficacy: 89.5 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 58.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P768533

CATALOG NUMBER: LD6D55D010-EU6DR6555659040-6LBDP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P768533

CATALOG NUMBER: LD6D55D010-EU6DR6555659040-6LBDP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93																			
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87																			
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80																			
4	97	89	84	79	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	83	78	73	90	83	77	73	81	76	72	79	75	72	77	74	71	69																			
6	87	78	72	68	86	77	72	68	76	71	67	74	70	67	73	69	66	65																			
7	83	73	67	63	81	73	67	63	71	66	62	70	66	62	69	65	62	60																			
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	57																			
9	75	65	59	55	74	65	59	55	64	58	55	63	58	55	62	58	54	53																			
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	560136
5°	560598
10°	580338
15°	581298
20°	535181
25°	456003
30°	349082
35°	246625
40°	145582
45°	59103
50°	21417
55°	11944
60°	6840
65°	3775
70°	3961
75°	3082
80°	3209
85°	2758

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 59103 cd/sqm



TEST NUMBER: P768533

CATALOG NUMBER: LD6D55D010-EU6DR6555659040-6LBDP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	493.6	9.5
10°-20°	1424.0	27.3
20°-30°	1708.5	32.8
30°-40°	1148.1	22.1
40°-50°	343.7	6.6
50°-60°	60.7	1.2
60°-70°	17.2	0.3
70°-80°	8.5	0.2
80°-90°	2.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3626.1	69.6
0°-40°	4774.2	91.7
0°-60°	5178.6	99.5
0°-90°	5207.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5207.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5127	
5°	5111	494
15°	5139	1424
25°	3782	1708
35°	1849	1148
45°	382	344
55°	63	61
65°	15	17
75°	7	8
85°	2	3
90°	0	



TEST NUMBER: P768533

CATALOG NUMBER: LD6D55D010-EU6DR6555659040-6LBDP1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	5126.6
2.5°	5148.4
5°	5111.3
7.5°	5188.5
10°	5230.8
12.5°	5220.6
15°	5139.0
17.5°	4939.4
20°	4602.8
22.5°	4206.5
25°	3782.5
27.5°	3303.8
30°	2766.9
32.5°	2280.3
35°	1849.0
37.5°	1422.8
40°	1020.7
42.5°	666.6
45°	382.5
47.5°	202.5
50°	126.0
52.5°	87.4
55°	62.7
57.5°	45.2
60°	31.3
62.5°	20.4
65°	14.6
67.5°	13.1
70°	12.4
72.5°	9.5
75°	7.3
77.5°	6.6
80°	5.1
82.5°	3.6
85°	2.2
87.5°	1.5
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)