

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P768610

Luminaire Tested: LD6D55D010-EU6DR7055659040-6LBDP1LI

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P768610
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D55D010-EU6DR7055659040-6LBDP1LI
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7299.7 lumens
Efficiency: N/A
Efficacy: 125.4 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 58.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P768610
CATALOG NUMBER: LD6D55D010-EU6DR7055659040-6LBDP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P768610
 CATALOG NUMBER: LD6D55D010-EU6DR7055659040-6LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10		0		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	896703
5°	870055
10°	845810
15°	834710
20°	779447
25°	585552
30°	413942
35°	146628
40°	77091
45°	82126
50°	85041
55°	86635
60°	87168
65°	85316
70°	80535
75°	74594
80°	66256
85°	53781

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 87197 cd/sqm



TEST NUMBER: P768610

CATALOG NUMBER: LD6D55D010-EU6DR7055659040-6LBDP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	748.2	10.3
10°-20°	2052.4	28.1
20°-30°	2260.4	31.0
30°-40°	863.6	11.8
40°-50°	407.8	5.6
50°-60°	405.4	5.6
60°-70°	324.6	4.4
70°-80°	186.5	2.6
80°-90°	50.7	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5061.0	69.3
0°-40°	5924.7	81.2
0°-60°	6737.9	92.3
0°-90°	7299.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7299.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8207	
5°	7933	748
15°	7379	2052
25°	4857	2260
35°	1099	864
45°	532	408
55°	455	405
65°	330	325
75°	177	187
85°	43	51
90°	0	



TEST NUMBER: P768610

CATALOG NUMBER: LD6D55D010-EU6DR7055659040-6LBDP1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	8207.0
2.5°	8121.2
5°	7932.8
7.5°	7775.6
10°	7623.6
12.5°	7494.9
15°	7379.3
17.5°	7099.9
20°	6703.6
22.5°	5848.6
25°	4857.1
27.5°	4228.2
30°	3281.0
32.5°	2119.3
35°	1099.3
37.5°	593.8
40°	540.5
42.5°	536.7
45°	531.5
47.5°	519.8
50°	500.3
52.5°	478.2
55°	454.8
57.5°	428.8
60°	398.9
62.5°	365.1
65°	330.0
67.5°	291.1
70°	252.1
72.5°	213.1
75°	176.7
77.5°	139.0
80°	105.3
82.5°	74.1
85°	42.9
87.5°	16.9
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)