

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P757177

Luminaire Tested: LD6D02D010-EU6DR300210IC9040-6LBDP1MW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P757177
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D02D010-EU6DR300210IC9040-6LBDP1MW
Description: 6 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 30° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 342.5 lumens
Efficiency: N/A
Efficacy: 67.2 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.49
Luminous Opening: Rectangular (W 0.38' x L: 0.38' x H: 0')
CIE Type: Direct

Input Watts (W): 5.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P757177

CATALOG NUMBER: LD6D02D010-EU6DR300210IC9040-6LBDP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P757177

CATALOG NUMBER: LD6D02D010-EU6DR300210IC9040-6LBDP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96																			
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92																			
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89																			
4	103	98	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85																			
5	100	94	89	86	98	93	89	86	91	88	85	90	86	84	88	86	83	82																			
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79																			
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77																			
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74																			
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	72																			
10	85	78	74	71	85	78	74	71	77	73	71	76	73	71	76	73	70	69																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	84305	84305	84305
5°	81884	81792	81892
10°	70923	70426	70908
15°	46278	46025	45795
20°	23011	23875	22979
25°	11587	13074	11351
30°	4640	5056	4039
35°	2149	2065	1729
40°	929	1029	879
45°	660	812	660
50°	226	595	238
55°	133	240	133
60°	92	107	92
65°	54	54	54
70°	45	22	45
75°	0	30	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°

Vertical Angle: 45°

Luminance: 812 cd/sqm



TEST NUMBER: P757177

CATALOG NUMBER: LD6D02D010-EU6DR300210IC9040-6LBDP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	96.9	28.3
10°-20°	156.0	45.5
20°-30°	67.4	19.7
30°-40°	15.4	4.5
40°-50°	5.3	1.5
50°-60°	1.3	0.4
60°-70°	0.3	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	320.2	93.5
0°-40°	335.6	98.0
0°-60°	342.2	99.9
0°-90°	342.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	342.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1101	1101	1101	1101	1101	
5°	1066	1065	1064	1067	1066	97
15°	584	577	581	579	578	156
25°	137	142	155	139	134	66
35°	23	24	22	22	18	16
45°	6	8	8	8	6	4
55°	1	1	2	1	1	1
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	



TEST NUMBER: P757177

CATALOG NUMBER: LD6D02D010-EU6DR300210IC9040-6LBDP1MW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1101.4	1101.4	1101.4	1101.4	1101.4
2.5°	1094.1	1093.4	1093.8	1094.3	1094.6
5°	1065.7	1064.7	1064.5	1066.7	1065.8
7.5°	1008.5	1007.0	1004.8	1009.8	1014.5
10°	912.5	910.9	906.1	908.5	912.3
12.5°	770.9	765.6	765.6	773.1	772.1
15°	584.0	577.0	580.8	578.9	577.9
17.5°	392.7	390.0	395.2	393.6	386.9
20°	282.5	283.2	293.1	288.1	282.1
22.5°	206.1	208.7	220.4	207.6	202.9
25°	137.2	142.4	154.8	138.8	134.4
27.5°	84.4	86.8	99.3	83.3	81.0
30°	52.5	51.3	57.2	49.1	45.7
32.5°	34.4	32.9	34.8	31.3	28.5
35°	23.0	23.5	22.1	21.9	18.5
37.5°	14.4	16.6	14.6	15.6	11.9
40°	9.3	12.0	10.3	11.4	8.8
42.5°	7.6	9.2	8.5	9.1	7.8
45°	6.1	7.5	7.5	7.5	6.1
47.5°	3.4	5.0	6.4	5.2	3.6
50°	1.9	2.5	5.0	2.6	2.0
52.5°	1.3	1.4	3.4	1.5	1.4
55°	1.0	1.0	1.8	1.1	1.0
57.5°	0.7	0.8	1.0	0.8	0.7
60°	0.6	0.6	0.7	0.6	0.6
62.5°	0.5	0.5	0.5	0.5	0.5
65°	0.3	0.3	0.3	0.3	0.3
67.5°	0.2	0.2	0.2	0.2	0.2
70°	0.2	0.1	0.1	0.1	0.2
72.5°	0.1	0.1	0.1	0.1	0.1
75°	0.0	0.0	0.1	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - - 90°-270°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)