

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P757111

Luminaire Tested: LD6D02D010-EU6DR250210IC9050-6LBDP1LI

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P757111
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-4)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D02D010-EU6DR250210IC9050-6LBDP1LI
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 25° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 364.6 lumens
Efficiency: N/A
Efficacy: 71.5 lumens/watt
Spacing Criteria (0/90/45): 0.42 / 0.42 / 0.45
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 5.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P757111

CATALOG NUMBER: LD6D02D010-EU6DR250210IC9050-6LBDP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P757111

CATALOG NUMBER: LD6D02D010-EU6DR250210IC9050-6LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20																	
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																								
RCR																																																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																																				
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96																																				
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92																																				
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89																																				
4	103	97	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85																																				
5	100	93	89	86	98	93	89	86	91	87	85	89	86	84	88	85	83	82																																				
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79																																				
7	93	87	82	79	92	86	82	79	85	81	78	84	80	78	83	80	78	77																																				
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74																																				
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	72																																				
10	85	78	74	71	85	78	74	71	77	73	71	76	73	71	76	73	70	69																																				

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	151075
5°	140706
10°	100362
15°	59114
20°	36777
25°	20181
30°	9235
35°	3495
40°	1583
45°	958
50°	391
55°	248
60°	175
65°	129
70°	32
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 958 cd/sqm



TEST NUMBER: P757111

CATALOG NUMBER: LD6D02D010-EU6DR250210IC9050-6LBDP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	110.3	30.2
10°-20°	149.3	41.0
20°-30°	79.0	21.7
30°-40°	19.5	5.3
40°-50°	4.8	1.3
50°-60°	1.2	0.3
60°-70°	0.4	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	338.6	92.9
0°-40°	358.1	98.2
0°-60°	364.1	99.9
0°-90°	364.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	364.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1383	
5°	1283	110
15°	523	149
25°	167	79
35°	26	19
45°	6	5
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P757111

CATALOG NUMBER: LD6D02D010-EU6DR250210IC9050-6LBDP1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	1382.7
2.5°	1360.0
5°	1282.9
7.5°	1128.1
10°	904.6
12.5°	683.9
15°	522.6
17.5°	407.3
20°	316.3
22.5°	237.3
25°	167.4
27.5°	112.3
30°	73.2
32.5°	44.5
35°	26.2
37.5°	16.0
40°	11.1
42.5°	8.5
45°	6.2
47.5°	3.7
50°	2.3
52.5°	1.7
55°	1.3
57.5°	1.0
60°	0.8
62.5°	0.6
65°	0.5
67.5°	0.2
70°	0.1
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)