

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P768755

Luminaire Tested: LD6D60D010-EU6DR3055659035-6LBS1B

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P768755
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D60D010-EU6DR3055659035-6LBS1B
Description: 6 INCH ROUND SHALLOW SPECULAR BLACK TRIM, WITH 30° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6973.1 lumens
Efficiency: N/A
Efficacy: 108.3 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.49
Luminous Opening: Rectangular (W 0.38' x L: 0.38' x H: 0')
CIE Type: Direct


Input Watts (W): 64.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P768755
CATALOG NUMBER: LD6D60D010-EU6DR3055659035-6LBS1B

Luminous Intensity Polar Plot





TEST NUMBER: P768755

CATALOG NUMBER: LD6D60D010-EU6DR3055659035-6LBS1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96																			
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92																			
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89																			
4	103	98	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85																			
5	100	94	89	86	98	93	89	86	91	88	85	90	86	84	88	86	83	82																			
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79																			
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77																			
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74																			
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	72																			
10	85	78	74	71	85	78	74	71	77	73	71	76	73	71	76	73	70	69																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1716256	1716256	1716256
5°	1666983	1665039	1667067
10°	1443859	1433677	1443517
15°	942047	936984	932277
20°	468436	486014	467809
25°	235962	266088	231132
30°	94474	102942	82313
35°	43824	41965	35181
40°	18915	21013	17816
45°	13347	16562	13466
50°	4585	12063	4847
55°	2642	4991	2789
60°	1852	2189	1852
65°	1195	1195	1195
70°	739	492	739
75°	0	325	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°
 Vertical Angle: 45°
 Luminance: 16562 cd/sqm



TEST NUMBER: P768755
 CATALOG NUMBER: LD6D60D010-EU6DR3055659035-6LBS1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1971.7	28.3
10°-20°	3175.4	45.5
20°-30°	1372.2	19.7
30°-40°	312.7	4.5
40°-50°	107.4	1.5
50°-60°	26.2	0.4
60°-70°	6.8	0.1
70°-80°	0.7	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6519.2	93.5
0°-40°	6832.0	98.0
0°-60°	6965.6	99.9
0°-90°	6973.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6973.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	22422	22422	22422	22422	22422	
5°	21695	21674	21670	21715	21696	1973
15°	11888	11745	11824	11786	11765	3183
25°	2794	2900	3151	2826	2737	1337
35°	469	479	449	446	376	318
45°	123	153	153	153	124	88
55°	20	21	37	22	21	19
65°	7	7	7	7	7	6
75°	0	0	1	0	0	1
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P768755

CATALOG NUMBER: LD6D60D010-EU6DR3055659035-6LBS1B

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	22422.0	22422.0	22422.0	22422.0	22422.0
2.5°	22273.3	22257.9	22266.7	22277.7	22282.1
5°	21695.4	21674.5	21670.1	21715.2	21696.5
7.5°	20529.6	20499.9	20454.7	20557.1	20652.9
10°	18576.7	18543.7	18445.7	18494.1	18572.3
12.5°	15693.6	15586.8	15584.6	15738.7	15717.8
15°	11888.0	11744.9	11824.1	11785.6	11764.7
17.5°	7994.3	7939.3	8045.0	8013.0	7875.4
20°	5750.8	5765.1	5966.6	5865.3	5743.1
22.5°	4196.4	4248.1	4487.0	4226.1	4130.4
25°	2793.9	2899.6	3150.6	2825.9	2736.7
27.5°	1718.4	1766.9	2021.1	1696.4	1648.0
30°	1068.9	1044.7	1164.7	999.6	931.3
32.5°	701.2	670.4	708.9	636.3	581.2
35°	469.0	478.9	449.1	445.8	376.5
37.5°	292.8	336.9	297.2	317.0	242.2
40°	189.3	244.4	210.3	232.3	178.3
42.5°	155.2	188.2	172.8	183.8	158.5
45°	123.3	153.0	153.0	153.0	124.4
47.5°	68.3	102.4	131.0	104.6	72.7
50°	38.5	51.7	101.3	53.9	40.7
52.5°	26.4	29.7	69.4	30.8	27.5
55°	19.8	20.9	37.4	22.0	20.9
57.5°	15.4	16.5	19.8	16.5	15.4
60°	12.1	12.1	14.3	13.2	12.1
62.5°	8.8	8.8	9.9	8.8	8.8
65°	6.6	6.6	6.6	6.6	6.6
67.5°	3.3	4.4	4.4	4.4	4.4
70°	3.3	2.2	2.2	2.2	3.3
72.5°	2.2	1.1	1.1	1.1	1.1
75°	0.0	0.0	1.1	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - - 90°-270°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)