

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P768757

Luminaire Tested: LD6D60D010-EU6DR3055659035-6LBS1LI

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P768757
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D60D010-EU6DR3055659035-6LBS1LI
Description: 6 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 30° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7809.2 lumens
Efficiency: N/A
Efficacy: 121.3 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.49
Luminous Opening: Rectangular (W 0.38' x L: 0.38' x H: 0')
CIE Type: Direct


Input Watts (W): 64.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P768757
CATALOG NUMBER: LD6D60D010-EU6DR3055659035-6LBS1LI

Luminous Intensity Polar Plot





TEST NUMBER: P768757

CATALOG NUMBER: LD6D60D010-EU6DR3055659035-6LBS1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96																			
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92																			
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89																			
4	103	98	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85																			
5	100	94	89	86	98	93	89	86	91	88	85	90	86	84	88	86	83	82																			
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79																			
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77																			
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74																			
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	72																			
10	85	78	74	71	85	78	74	71	77	73	71	76	73	71	76	73	70	69																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1922043	1922043	1922043
5°	1866864	1864681	1866956
10°	1616990	1605588	1616601
15°	1055001	1049335	1044066
20°	524608	544288	523899
25°	264255	297996	258842
30°	105805	115280	92185
35°	49076	47001	39395
40°	21183	23531	19954
45°	14949	18554	15079
50°	5132	13504	5430
55°	2963	5592	3123
60°	2082	2449	2082
65°	1340	1340	1340
70°	828	559	828
75°	0	355	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°

Vertical Angle: 45°

Luminance: 18554 cd/sqm



TEST NUMBER: P768757

CATALOG NUMBER: LD6D60D010-EU6DR3055659035-6LBS1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	2208.1	28.3
10°-20°	3556.1	45.5
20°-30°	1536.7	19.7
30°-40°	350.2	4.5
40°-50°	120.3	1.5
50°-60°	29.4	0.4
60°-70°	7.6	0.1
70°-80°	0.8	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	7300.9	93.5
0°-40°	7651.2	98.0
0°-60°	7800.8	99.9
0°-90°	7809.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7809.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	25110	25110	25110	25110	25110	
5°	24297	24273	24268	24319	24298	2210
15°	13313	13153	13242	13199	13175	3565
25°	3129	3247	3528	3165	3065	1498
35°	525	536	503	499	422	356
45°	138	171	171	171	139	98
55°	22	23	42	25	23	22
65°	7	7	7	7	7	7
75°	0	0	1	0	0	1
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P768757

CATALOG NUMBER: LD6D60D010-EU6DR3055659035-6LBS1LI

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	25110.5	25110.5	25110.5	25110.5	25110.5
2.5°	24944.0	24926.8	24936.6	24949.0	24953.9
5°	24296.8	24273.4	24268.4	24319.0	24298.0
7.5°	22991.2	22957.9	22907.4	23022.0	23129.3
10°	20804.2	20767.2	20657.5	20711.7	20799.2
12.5°	17575.4	17455.8	17453.3	17625.9	17602.5
15°	13313.4	13153.2	13241.9	13198.8	13175.4
17.5°	8952.9	8891.2	9009.6	8973.8	8819.7
20°	6440.4	6456.4	6682.0	6568.6	6431.7
22.5°	4699.6	4757.5	5025.1	4732.9	4625.6
25°	3128.9	3247.3	3528.4	3164.7	3064.8
27.5°	1924.5	1978.7	2263.5	1899.8	1845.6
30°	1197.1	1170.0	1304.3	1119.4	1043.0
32.5°	785.3	750.8	793.9	712.6	650.9
35°	525.2	536.3	503.0	499.3	421.6
37.5°	327.9	377.2	332.9	355.1	271.2
40°	212.0	273.7	235.5	260.1	199.7
42.5°	173.8	210.8	193.6	205.9	177.5
45°	138.1	171.4	171.4	171.4	139.3
47.5°	76.4	114.7	146.7	117.1	81.4
50°	43.1	57.9	113.4	60.4	45.6
52.5°	29.6	33.3	77.7	34.5	30.8
55°	22.2	23.4	41.9	24.7	23.4
57.5°	17.3	18.5	22.2	18.5	17.3
60°	13.6	13.6	16.0	14.8	13.6
62.5°	9.9	9.9	11.1	9.9	9.9
65°	7.4	7.4	7.4	7.4	7.4
67.5°	3.7	4.9	4.9	4.9	4.9
70°	3.7	2.5	2.5	2.5	3.7
72.5°	2.5	1.2	1.2	1.2	1.2
75°	0.0	0.0	1.2	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - - 90°-270°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)