

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P757814

Luminaire Tested: LD6D02D010-EU6DR700210IC9050-6LBDP1MW

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P757814
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D02D010-EU6DR700210IC9050-6LBDP1MW
Description: 6 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 306.3 lumens
Efficiency: N/A
Efficacy: 60.1 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 5.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P757814
CATALOG NUMBER: LD6D02D010-EU6DR700210IC9050-6LBDP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P757814

CATALOG NUMBER: LD6D02D010-EU6DR700210IC9050-6LBDP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	88	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	37640
5°	36512
10°	35492
15°	35032
20°	32719
25°	24581
30°	17373
35°	6149
40°	3238
45°	3446
50°	3570
55°	3638
60°	3649
65°	3594
70°	3386
75°	3124
80°	2769
85°	2257

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 3660 cd/sqm



TEST NUMBER: P757814

CATALOG NUMBER: LD6D02D010-EU6DR700210IC9050-6LBDP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	31.4	10.3
10°-20°	86.1	28.1
20°-30°	94.9	31.0
30°-40°	36.2	11.8
40°-50°	17.1	5.6
50°-60°	17.0	5.6
60°-70°	13.6	4.4
70°-80°	7.8	2.5
80°-90°	2.1	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	212.4	69.3
0°-40°	248.6	81.2
0°-60°	282.8	92.3
0°-90°	306.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	306.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	344	
5°	333	31
15°	310	86
25°	204	95
35°	46	36
45°	22	17
55°	19	17
65°	14	14
75°	7	8
85°	2	2
90°	0	



TEST NUMBER: P757814

CATALOG NUMBER: LD6D02D010-EU6DR700210IC9050-6LBDP1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	344.5
2.5°	340.8
5°	332.9
7.5°	326.4
10°	319.9
12.5°	314.5
15°	309.7
17.5°	298.0
20°	281.4
22.5°	245.5
25°	203.9
27.5°	177.4
30°	137.7
32.5°	88.9
35°	46.1
37.5°	24.9
40°	22.7
42.5°	22.5
45°	22.3
47.5°	21.8
50°	21.0
52.5°	20.1
55°	19.1
57.5°	18.0
60°	16.7
62.5°	15.3
65°	13.9
67.5°	12.2
70°	10.6
72.5°	8.9
75°	7.4
77.5°	5.8
80°	4.4
82.5°	3.1
85°	1.8
87.5°	0.7
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)