

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P768781

Luminaire Tested: LD6D60D010-EU6DR3055659050-6LBS1B

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P768781
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D60D010-EU6DR3055659050-6LBS1B
Description: 6 INCH ROUND SHALLOW SPECULAR BLACK TRIM, WITH 30° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7351.3 lumens
Efficiency: N/A
Efficacy: 114.2 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.49
Luminous Opening: Rectangular (W 0.38' x L: 0.38' x H: 0')
CIE Type: Direct


Input Watts (W): 64.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P768781
CATALOG NUMBER: LD6D60D010-EU6DR3055659050-6LBS1B

Luminous Intensity Polar Plot





TEST NUMBER: P768781

CATALOG NUMBER: LD6D60D010-EU6DR3055659050-6LBS1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96																			
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92																			
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89																			
4	103	98	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85																			
5	100	94	89	86	98	93	89	86	91	88	85	90	86	84	88	86	83	82																			
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79																			
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77																			
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74																			
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	72																			
10	85	78	74	71	85	78	74	71	77	73	71	76	73	71	76	73	70	69																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1809325	1809325	1809325
5°	1757380	1755329	1757472
10°	1522159	1511425	1521801
15°	993136	987803	982834
20°	493842	512365	493174
25°	248758	280522	243665
30°	99601	108528	86776
35°	46198	44245	37087
40°	19944	22152	18785
45°	14072	17461	14191
50°	4835	12718	5109
55°	2789	5271	2949
60°	1960	2312	1960
65°	1268	1268	1268
70°	783	515	783
75°	0	355	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°

Vertical Angle: 45°

Luminance: 17461 cd/sqm



TEST NUMBER: P768781

CATALOG NUMBER: LD6D60D010-EU6DR3055659050-6LBS1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	2078.6	28.3
10°-20°	3347.6	45.5
20°-30°	1446.6	19.7
30°-40°	329.7	4.5
40°-50°	113.2	1.5
50°-60°	27.7	0.4
60°-70°	7.2	0.1
70°-80°	0.8	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6872.8	93.5
0°-40°	7202.5	98.0
0°-60°	7343.3	99.9
0°-90°	7351.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7351.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	23638	23638	23638	23638	23638	
5°	22872	22850	22845	22893	22873	2080
15°	12533	12382	12465	12425	12403	3356
25°	2945	3057	3322	2979	2885	1410
35°	494	505	474	470	397	335
45°	130	161	161	161	131	92
55°	21	22	40	23	22	20
65°	7	7	7	7	7	7
75°	0	0	1	0	0	1
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P768781

CATALOG NUMBER: LD6D60D010-EU6DR3055659050-6LBS1B

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	23637.9	23637.9	23637.9	23637.9	23637.9
2.5°	23481.2	23464.9	23474.2	23485.8	23490.5
5°	22871.9	22849.9	22845.2	22892.8	22873.1
7.5°	21642.9	21611.6	21564.0	21671.9	21772.9
10°	19584.1	19549.3	19446.0	19497.1	19579.5
12.5°	16544.6	16432.1	16429.8	16592.2	16570.2
15°	12532.7	12381.8	12465.4	12424.7	12402.7
17.5°	8427.8	8369.8	8481.2	8447.6	8302.5
20°	6062.7	6077.7	6290.1	6183.4	6054.5
22.5°	4424.0	4478.5	4730.4	4455.3	4354.3
25°	2945.4	3056.9	3321.5	2979.1	2885.1
27.5°	1811.6	1862.7	2130.8	1788.4	1737.3
30°	1126.9	1101.4	1227.9	1053.8	981.8
32.5°	739.3	706.8	747.4	670.8	612.8
35°	494.4	504.8	473.5	470.0	396.9
37.5°	308.7	355.1	313.3	334.2	255.3
40°	199.6	257.6	221.7	244.9	188.0
42.5°	163.6	198.5	182.2	193.8	167.1
45°	130.0	161.3	161.3	161.3	131.1
47.5°	72.0	107.9	138.1	110.3	76.6
50°	40.6	54.5	106.8	56.9	42.9
52.5°	27.9	31.3	73.1	32.5	29.0
55°	20.9	22.1	39.5	23.2	22.1
57.5°	16.2	17.4	20.9	17.4	16.2
60°	12.8	12.8	15.1	13.9	12.8
62.5°	9.3	9.3	10.4	9.3	9.3
65°	7.0	7.0	7.0	7.0	7.0
67.5°	3.5	4.6	4.6	4.6	4.6
70°	3.5	2.3	2.3	2.3	3.5
72.5°	2.3	1.2	1.2	1.2	1.2
75°	0.0	0.0	1.2	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - 90°-270°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)