

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P762997

Luminaire Tested: LD6D25D010-EU6DR2015309040-6LBS1H

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P762997
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-36)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D25D010-EU6DR2015309040-6LBS1H
Description: 6 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 20° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3431.3 lumens
Efficiency: N/A
Efficacy: 136.7 lumens/watt
Spacing Criteria (0/90/45): 0.34 / 0.34 / 0.36
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 25.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P762997
CATALOG NUMBER: LD6D25D010-EU6DR2015309040-6LBS1H

Luminous Intensity Polar Plot





TEST NUMBER: P762997

CATALOG NUMBER: LD6D25D010-EU6DR2015309040-6LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20																	
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR																																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100									100																		
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97	98	96	95	94	94	92	91	91	89	88	86	85															
2	111	108	105	102	109	106	104	101	103	101	99	100	99	97	98	96	95	94	94	92	91	89	88	86	85	83	82	81	79																
3	108	103	100	97	106	102	99	96	100	97	95	97	95	93	95	93	92	91	91	89	88	86	85	83	82	81	79	77																	
4	105	99	96	93	103	98	95	92	96	93	91	95	92	90	93	91	89	88	86	85	83	82	81	79	77	75																			
5	102	96	92	89	100	95	91	89	94	90	88	92	89	87	91	88	86	85	83	82	81	79	77	75	73																				
6	99	93	89	86	98	92	88	86	91	87	85	90	87	84	88	86	84	83	81	80	79	77	75	73	71																				
7	96	90	86	83	95	89	86	83	88	85	82	87	84	82	86	84	82	81	79	77	75	73	71	69																					
8	94	87	83	81	93	87	83	80	86	83	80	85	82	80	84	82	80	79	77	75	73	71	69	67																					
9	91	85	81	78	91	85	81	78	84	80	78	83	80	78	82	80	78	77	75	73	71	69	67	65																					
10	89	83	79	76	88	82	79	76	82	78	76	81	78	76	81	78	76	75	73	71	69	67	65	63																					

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2133884
5°	1925158
10°	1080506
15°	549241
20°	232546
25°	107343
30°	56824
35°	30625
40°	16374
45°	9673
50°	5609
55°	2991
60°	1901
65°	1344
70°	543
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 9673 cd/sqm



TEST NUMBER: P762997

CATALOG NUMBER: LD6D25D010-EU6DR2015309040-6LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1390.5	40.5
10°-20°	1369.2	39.9
20°-30°	447.3	13.0
30°-40°	152.3	4.4
40°-50°	51.2	1.5
50°-60°	15.4	0.4
60°-70°	5.1	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3207.0	93.5
0°-40°	3359.3	97.9
0°-60°	3426.0	99.8
0°-90°	3431.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3431.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	19530	
5°	17553	###
15°	4856	1369
25°	890	447
35°	230	152
45°	63	51
55°	16	15
65°	5	5
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P762997

CATALOG NUMBER: LD6D25D010-EU6DR2015309040-6LBS1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	19530.2
0.5°	19530.2
1°	19505.8
1.5°	19457.1
2°	19368.4
2.5°	19250.2
3°	19083.2
3.5°	18850.2
4°	18504.1
4.5°	18083.2
5°	17552.8
5.5°	16855.4
6°	16140.7
6.5°	15321.5
7°	14519.8
7.5°	13580.7
8°	12742.4
8.5°	11899.0
9°	11119.9
9.5°	10405.1
10°	9739.0
12.5°	6993.0
15°	4855.6
17.5°	3172.1
20°	2000.0
22.5°	1295.6
25°	890.4
27.5°	626.1
30°	450.4
32.5°	323.5
35°	229.6
37.5°	160.0
40°	114.8
42.5°	83.5
45°	62.6
47.5°	48.7
50°	33.0
52.5°	20.9
55°	15.7
57.5°	12.2
60°	8.7
62.5°	7.0
65°	5.2



TEST NUMBER: P762997
CATALOG NUMBER: LD6D25D010-EU6DR2015309040-6LBS1H

CANDELA DISTRIBUTION (continued):

	0°
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





67.5°		3.5
70°		1.7

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)