

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P769915

Luminaire Tested: LD6D65D010-EU6DR5555659030-6LBS1MW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P769915
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-52)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D65D010-EU6DR5555659030-6LBS1MW
Description: 6 INCH ROUND SHALLOW MATTE WHITE TRIM, WITH 55° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8098.6 lumens
Efficiency: N/A
Efficacy: 111.2 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 0.89 / 0.87
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 72.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P769915
CATALOG NUMBER: LD6D65D010-EU6DR5555659030-6LBS1MW

Luminous Intensity Polar Plot





TEST NUMBER: P769915
 CATALOG NUMBER: LD6D65D010-EU6DR5555659030-6LBS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100	
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94			94	
2	108	103	99	96	106	101	98	95	98	95	92	95	93	90	92	90	89	87			87	
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81			81	
4	97	90	84	80	95	88	83	79	86	82	78	84	81	78	82	79	77	75			75	
5	92	84	78	74	91	83	77	73	81	76	73	79	75	72	78	74	71	70			70	
6	88	79	73	68	86	78	72	68	76	71	68	75	70	67	74	70	67	65			65	
7	83	74	68	64	82	73	67	63	72	67	63	71	66	63	70	65	62	61			61	
8	79	69	63	59	78	69	63	59	68	63	59	67	62	59	66	62	58	57			57	
9	75	66	60	56	74	65	59	55	64	59	55	63	58	55	62	58	55	54			54	
10	72	62	56	52	71	61	56	52	61	56	52	60	55	52	59	55	52	50			50	

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	992230
5°	952818
10°	949234
15°	921967
20°	826665
25°	683202
30°	516072
35°	374192
40°	239475
45°	109368
50°	35764
55°	15430
60°	6643
65°	879
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 109368 cd/sqm



TEST NUMBER: P769915

CATALOG NUMBER: LD6D65D010-EU6DR5555659030-6LBS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	826.7	10.2
10°-20°	2256.1	27.9
20°-30°	2571.0	31.7
30°-40°	1750.3	21.6
40°-50°	603.1	7.4
50°-60°	83.4	1.0
60°-70°	8.1	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5653.8	69.8
0°-40°	7404.0	91.4
0°-60°	8090.5	99.9
0°-90°	8098.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8098.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	9081	
5°	8687	827
15°	8151	2256
25°	5667	2571
35°	2805	1750
45°	708	603
55°	81	83
65°	3	8
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P769915

CATALOG NUMBER: LD6D65D010-EU6DR5555659030-6LBS1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	9081.3
2.5°	8873.1
5°	8687.4
7.5°	8596.3
10°	8555.8
12.5°	8420.7
15°	8150.7
17.5°	7721.9
20°	7109.7
22.5°	6403.1
25°	5667.1
27.5°	4900.8
30°	4090.5
32.5°	3404.1
35°	2805.4
37.5°	2236.0
40°	1679.0
42.5°	1163.6
45°	707.8
47.5°	381.5
50°	210.4
52.5°	124.9
55°	81.0
57.5°	51.8
60°	30.4
62.5°	13.5
65°	3.4
67.5°	1.1
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)