

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P770071

Luminaire Tested: LD6D65D010-EU6DR6555659030-6LBS1MW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P770071
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D65D010-EU6DR6555659030-6LBS1MW
Description: 6 INCH ROUND SHALLOW MATTE WHITE TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6940.4 lumens
Efficiency: N/A
Efficacy: 95.3 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct


Input Watts (W): 72.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P770071
CATALOG NUMBER: LD6D65D010-EU6DR6555659030-6LBS1MW

Luminous Intensity Polar Plot





TEST NUMBER: P770071

CATALOG NUMBER: LD6D65D010-EU6DR6555659030-6LBS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93																			
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85																			
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78																			
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72																			
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66																			
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61																			
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56																			
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52																			
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49																			
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	368044
5°	367116
10°	366800
15°	355493
20°	323632
25°	282022
30°	234566
35°	185860
40°	134146
45°	84743
50°	44176
55°	23481
60°	12335
65°	6785
70°	2852
75°	3137
80°	2186
85°	1876

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 84743 cd/sqm



TEST NUMBER: P770071

CATALOG NUMBER: LD6D65D010-EU6DR6555659030-6LBS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	595.9	8.6
10°-20°	1631.9	23.5
20°-30°	1994.7	28.7
30°-40°	1618.5	23.3
40°-50°	806.5	11.6
50°-60°	225.0	3.2
60°-70°	51.1	0.7
70°-80°	13.3	0.2
80°-90°	3.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4222.6	60.8
0°-40°	5841.1	84.2
0°-60°	6872.6	99.0
0°-90°	6940.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6940.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6302	
5°	6262	596
15°	5879	1632
25°	4376	1995
35°	2607	1618
45°	1026	807
55°	231	225
65°	49	51
75°	14	13
85°	3	3
90°	0	



TEST NUMBER: P770071

CATALOG NUMBER: LD6D65D010-EU6DR6555659030-6LBS1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	6301.7
2.5°	6297.0
5°	6261.9
7.5°	6241.5
10°	6185.0
12.5°	6070.2
15°	5879.4
17.5°	5581.2
20°	5207.1
22.5°	4803.4
25°	4376.4
27.5°	3919.9
30°	3478.2
32.5°	3042.0
35°	2606.8
37.5°	2172.5
40°	1759.5
42.5°	1372.4
45°	1026.0
47.5°	714.9
50°	486.2
52.5°	335.2
55°	230.6
57.5°	155.6
60°	105.6
62.5°	73.2
65°	49.1
67.5°	25.0
70°	16.7
72.5°	15.7
75°	13.9
77.5°	9.3
80°	6.5
82.5°	4.6
85°	2.8
87.5°	1.9
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)