

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P762934

Luminaire Tested: LD6D25D010-EU6DR1515309050-6LBS1MW

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P762934  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-21)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD6D25D010-EU6DR1515309050-6LBS1MW  
Description: 6 INCH ROUND SHALLOW MATTE WHITE TRIM, WITH 15° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3070.1 lumens  
Efficiency: N/A  
Efficacy: 122.3 lumens/watt  
Spacing Criteria (0/90/45): 0.22 / 0.22 / 0.23  
Luminous Opening: Vertical Cylinder (Dia: 0.35' x H: 0.35')  
CIE Type: Direct

Input Watts (W): 25.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight



TEST NUMBER: P762934  
CATALOG NUMBER: LD6D25D010-EU6DR1515309050-6LBS1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P762934

CATALOG NUMBER: LD6D25D010-EU6DR1515309050-6LBS1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						100													
1	116	114	112	111	113	112	110	109	108	107	106	104	103	103	101	100	100	98						98													
2	113	110	107	105	111	108	106	104	105	103	102	102	101	100	100	98	98	96						96													
3	110	106	103	101	108	105	102	100	103	100	99	100	99	97	98	97	96	94						94													
4	108	103	100	98	106	102	99	97	100	98	96	99	97	95	97	95	94	93						93													
5	106	101	98	95	104	100	97	95	98	96	94	97	95	93	96	94	92	92						92													
6	104	99	95	93	102	98	95	93	97	94	92	96	93	92	95	93	91	90						90													
7	102	97	94	91	101	96	93	91	95	93	91	94	92	90	93	91	90	89						89													
8	100	95	92	90	99	95	92	90	94	91	89	93	91	89	92	90	89	88						88													
9	99	93	90	88	98	93	90	88	92	90	88	92	89	88	91	89	88	87						87													
10	97	92	89	87	96	92	89	87	91	89	87	91	88	87	90	88	86	86						86													

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	4706698	4706698	4706698
5°	2765881	2730067	2751664
10°	825483	831268	843995
15°	205330	209334	202872
20°	61433	71145	62742
25°	21656	27592	21937
30°	7952	10476	8087
35°	3987	4502	3856
40°	2514	2770	2514
45°	1862	1981	1862
50°	1474	1474	1474
55°	1232	1232	1232
60°	997	997	997
65°	757	757	757
70°	651	651	651
75°	401	401	537
80°	276	276	276
85°	149	149	149

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 45°  
 Vertical Angle: 45°  
 Luminance: 1981 cd/sqm



TEST NUMBER: P762934

CATALOG NUMBER: LD6D25D010-EU6DR1515309050-6LBS1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	1991.2	64.9
10°-20°	819.0	26.7
20°-30°	162.7	5.3
30°-40°	40.6	1.3
40°-50°	21.3	0.7
50°-60°	15.8	0.5
60°-70°	11.2	0.4
70°-80°	6.4	0.2
80°-90°	1.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2972.9	96.8
0°-40°	3013.5	98.2
0°-60°	3050.7	99.4
0°-90°	3070.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3070.1	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	41830	41830	41830	41830	41830	
5°	27216	26936	26863	27049	27076	1987
15°	2364	2408	2410	2368	2336	811
25°	278	315	354	313	282	146
35°	55	58	62	58	53	37
45°	27	27	28	27	27	21
55°	18	18	18	18	18	16
65°	11	11	11	11	11	11
75°	5	5	5	5	7	6
85°	2	2	2	2	2	2
90°	0	0	0	0	0	



TEST NUMBER: P762934

CATALOG NUMBER: LD6D25D010-EU6DR1515309050-6LBS1MW

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	41829.9	41829.9	41829.9	41829.9	41829.9
2.5°	37732.3	37764.1	37776.5	37813.7	37951.8
5°	27215.5	26935.7	26863.1	27049.0	27075.6
7.5°	16121.4	16178.1	16385.2	16431.3	16264.8
10°	8846.9	8919.5	8908.9	8972.7	9045.3
12.5°	4524.4	4467.7	4450.0	4522.6	4421.7
15°	2364.0	2408.3	2410.1	2367.6	2335.7
17.5°	1271.4	1322.8	1407.8	1338.7	1232.5
20°	750.8	796.9	869.5	812.8	766.8
22.5°	464.0	501.1	552.5	508.2	471.0
25°	278.0	315.2	354.2	313.4	281.6
27.5°	164.7	196.6	221.4	194.8	162.9
30°	106.2	124.0	139.9	122.2	108.0
32.5°	74.4	81.5	88.5	81.5	74.4
35°	54.9	58.4	62.0	58.4	53.1
37.5°	42.5	46.0	47.8	44.3	40.7
40°	35.4	37.2	39.0	37.2	35.4
42.5°	30.1	31.9	31.9	31.9	30.1
45°	26.6	26.6	28.3	26.6	26.6
47.5°	23.0	23.0	24.8	23.0	23.0
50°	21.2	21.2	21.2	21.2	21.2
52.5°	19.5	19.5	19.5	19.5	19.5
55°	17.7	17.7	17.7	17.7	17.7
57.5°	15.9	15.9	15.9	15.9	15.9
60°	14.2	14.2	14.2	14.2	14.2
62.5°	12.4	12.4	12.4	12.4	12.4
65°	10.6	10.6	10.6	10.6	10.6
67.5°	10.6	10.6	10.6	10.6	10.6
70°	8.9	8.9	8.9	8.9	8.9
72.5°	7.1	7.1	7.1	7.1	7.1
75°	5.3	5.3	5.3	5.3	7.1
77.5°	5.3	5.3	5.3	5.3	5.3
80°	3.5	3.5	3.5	3.5	3.5
82.5°	3.5	3.5	3.5	3.5	3.5
85°	1.8	1.8	1.8	1.8	1.8
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report







— 0°-180°    - - 45°-225°    - - - - 90°-270°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)