

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P769550

Luminaire Tested: LD6D65D010-EU6DR3055659040-6LBS1LI

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P769550
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D65D010-EU6DR3055659040-6LBS1LI
Description: 6 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 30° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9040.7 lumens
Efficiency: N/A
Efficacy: 124.2 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.49
Luminous Opening: Rectangular (W 0.38' x L: 0.38' x H: 0')
CIE Type: Direct


Input Watts (W): 72.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P769550
CATALOG NUMBER: LD6D65D010-EU6DR3055659040-6LBS1LI

Luminous Intensity Polar Plot





TEST NUMBER: P769550

CATALOG NUMBER: LD6D65D010-EU6DR3055659040-6LBS1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96																			
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92																			
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89																			
4	103	98	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85																			
5	100	94	89	86	98	93	89	86	91	88	85	90	86	84	88	86	83	82																			
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79																			
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77																			
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74																			
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	72																			
10	85	78	74	71	85	78	74	71	77	73	71	76	73	71	76	73	70	69																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2225124	2225124	2225124
5°	2161244	2158724	2161360
10°	1871972	1858766	1871529
15°	1221365	1214804	1208702
20°	607326	630117	606512
25°	305926	344987	299659
30°	122492	133461	106716
35°	56813	54411	45609
40°	24530	27238	23102
45°	17309	21477	17461
50°	5954	15635	6287
55°	3430	6472	3616
60°	2403	2847	2403
65°	1558	1558	1558
70°	962	649	962
75°	0	414	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°
 Vertical Angle: 45°
 Luminance: 21477 cd/sqm



TEST NUMBER: P769550

CATALOG NUMBER: LD6D65D010-EU6DR3055659040-6LBS1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	2556.3	28.3
10°-20°	4116.9	45.5
20°-30°	1779.0	19.7
30°-40°	405.5	4.5
40°-50°	139.2	1.5
50°-60°	34.0	0.4
60°-70°	8.8	0.1
70°-80°	0.9	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	8452.2	93.5
0°-40°	8857.7	98.0
0°-60°	9030.9	99.9
0°-90°	9040.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	9040.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	29070	29070	29070	29070	29070	
5°	28128	28101	28095	28154	28130	2558
15°	15413	15227	15330	15280	15253	4127
25°	3622	3759	4085	3664	3548	1734
35°	608	621	582	578	488	412
45°	160	198	198	198	161	113
55°	26	27	48	28	27	25
65°	9	9	9	9	9	8
75°	0	0	1	0	0	1
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P769550

CATALOG NUMBER: LD6D65D010-EU6DR3055659040-6LBS1LI

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	29070.1	29070.1	29070.1	29070.1	29070.1
2.5°	28877.4	28857.5	28868.9	28883.2	28888.9
5°	28128.1	28101.0	28095.3	28153.8	28129.6
7.5°	26616.7	26578.2	26519.6	26652.4	26776.5
10°	24084.8	24041.9	23914.9	23977.7	24079.1
12.5°	20346.8	20208.4	20205.5	20405.3	20378.2
15°	15412.8	15227.3	15330.0	15280.1	15253.0
17.5°	10364.7	10293.3	10430.3	10388.9	10210.5
20°	7455.9	7474.5	7735.7	7604.4	7445.9
22.5°	5440.7	5507.7	5817.5	5479.2	5355.0
25°	3622.3	3759.4	4084.8	3663.7	3548.1
27.5°	2227.9	2290.7	2620.4	2199.4	2136.6
30°	1385.9	1354.5	1510.0	1295.9	1207.4
32.5°	909.2	869.2	919.1	824.9	753.6
35°	608.0	620.9	582.3	578.0	488.1
37.5°	379.6	436.7	385.4	411.0	314.0
40°	245.5	316.8	272.6	301.1	231.2
42.5°	201.2	244.1	224.1	238.3	205.5
45°	159.9	198.4	198.4	198.4	161.3
47.5°	88.5	132.7	169.8	135.6	94.2
50°	50.0	67.1	131.3	69.9	52.8
52.5°	34.3	38.5	89.9	40.0	35.7
55°	25.7	27.1	48.5	28.5	27.1
57.5°	20.0	21.4	25.7	21.4	20.0
60°	15.7	15.7	18.6	17.1	15.7
62.5°	11.4	11.4	12.8	11.4	11.4
65°	8.6	8.6	8.6	8.6	8.6
67.5°	4.3	5.7	5.7	5.7	5.7
70°	4.3	2.9	2.9	2.9	4.3
72.5°	2.9	1.4	1.4	1.4	1.4
75°	0.0	0.0	1.4	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - - 90°-270°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)