

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P770014

Luminaire Tested: LD6D65D010-EU6DR6055659040-6LBDP1LI

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P770014  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD6D65D010-EU6DR6055659040-6LBDP1LI  
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 60° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 8820.0 lumens  
Efficiency: N/A  
Efficacy: 121.2 lumens/watt  
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 72.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight

TEST NUMBER: P770014

CATALOG NUMBER: LD6D65D010-EU6DR6055659040-6LBDP1LI

### Luminous Intensity Polar Plot





TEST NUMBER: P770014

CATALOG NUMBER: LD6D65D010-EU6DR6055659040-6LBDP1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93			93																
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86			86																
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80			80																
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75			75																
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70			70																
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66			66																
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62			62																
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59			59																
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55			55																
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53			53																

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1144485
5°	1172635
10°	1186792
15°	1130585
20°	996831
25°	806266
30°	545367
35°	273288
40°	44329
45°	43389
50°	44263
55°	44918
60°	46174
65°	47234
70°	48334
75°	48927
80°	47191
85°	39364

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 75°  
 Luminance: 48927 cd/sqm



TEST NUMBER: P770014

CATALOG NUMBER: LD6D65D010-EU6DR6055659040-6LBDP1LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	1021.8	11.6
10°-20°	2764.7	31.3
20°-30°	2974.6	33.7
30°-40°	1293.0	14.7
40°-50°	217.2	2.5
50°-60°	211.2	2.4
60°-70°	180.6	2.0
70°-80°	120.8	1.4
80°-90°	36.2	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6761.1	76.7
0°-40°	8054.1	91.3
0°-60°	8482.4	96.2
0°-90°	8820.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8820.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	10475	
5°	10692	###
15°	9995	2765
25°	6688	2975
35°	2049	1293
45°	281	217
55°	236	211
65°	183	181
75°	116	121
85°	31	36
90°	0	



TEST NUMBER: P770014

CATALOG NUMBER: LD6D65D010-EU6DR6055659040-6LBDP1LI

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	10474.8
2.5°	10769.3
5°	10691.6
7.5°	10716.1
10°	10697.0
12.5°	10476.2
15°	9995.0
17.5°	9348.8
20°	8573.2
22.5°	7743.0
25°	6687.9
27.5°	5349.2
30°	4322.7
32.5°	3331.7
35°	2048.9
37.5°	876.5
40°	310.8
42.5°	286.3
45°	280.8
47.5°	271.3
50°	260.4
52.5°	248.1
55°	235.8
57.5°	223.6
60°	211.3
62.5°	197.7
65°	182.7
67.5°	167.7
70°	151.3
72.5°	133.6
75°	115.9
77.5°	95.4
80°	75.0
82.5°	53.2
85°	31.4
87.5°	10.9
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)