

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P766937

Luminaire Tested: LD6D45BD010-EU6DR6540509027-6LBS1LI

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P766937
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D45BD010-EU6DR6540509027-6LBS1LI
Description: 6 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4609.9 lumens
Efficiency: N/A
Efficacy: 119.1 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct


Input Watts (W): 38.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P766937
CATALOG NUMBER: LD6D45BD010-EU6DR6540509027-6LBS1LI

Luminous Intensity Polar Plot





TEST NUMBER: P766937

CATALOG NUMBER: LD6D45BD010-EU6DR6540509027-6LBS1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100															
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93				93															
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85				85															
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78				78															
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72				72															
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66				66															
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61				61															
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56				56															
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52				52															
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49				49															
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46				46															

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	244455
5°	243841
10°	243630
15°	236125
20°	214959
25°	187325
30°	155804
35°	123452
40°	89103
45°	56289
50°	29339
55°	15599
60°	8188
65°	4505
70°	1895
75°	2076
80°	1446
85°	1206

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 56289 cd/sqm



TEST NUMBER: P766937

CATALOG NUMBER: LD6D45BD010-EU6DR6540509027-6LBS1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	395.8	8.6
10°-20°	1083.9	23.5
20°-30°	1324.9	28.7
30°-40°	1075.0	23.3
40°-50°	535.7	11.6
50°-60°	149.4	3.2
60°-70°	34.0	0.7
70°-80°	8.9	0.2
80°-90°	2.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2804.7	60.8
0°-40°	3879.7	84.2
0°-60°	4564.9	99.0
0°-90°	4609.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4609.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4186	
5°	4159	396
15°	3905	1084
25°	2907	1325
35°	1732	1075
45°	682	536
55°	153	149
65°	33	34
75°	9	9
85°	2	2
90°	0	



TEST NUMBER: P766937

CATALOG NUMBER: LD6D45BD010-EU6DR6540509027-6LBS1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	4185.6
2.5°	4182.6
5°	4159.2
7.5°	4145.7
10°	4108.1
12.5°	4031.9
15°	3905.2
17.5°	3707.1
20°	3458.6
22.5°	3190.4
25°	2906.9
27.5°	2603.7
30°	2310.3
32.5°	2020.6
35°	1731.5
37.5°	1443.0
40°	1168.7
42.5°	911.6
45°	681.5
47.5°	474.8
50°	322.9
52.5°	222.7
55°	153.2
57.5°	103.3
60°	70.1
62.5°	48.6
65°	32.6
67.5°	16.6
70°	11.1
72.5°	10.5
75°	9.2
77.5°	6.2
80°	4.3
82.5°	3.1
85°	1.8
87.5°	1.2
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)