

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P770168

Luminaire Tested: LD6D65D010-EU6DR7055659040-6LBDP1B

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P770168  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD6D65D010-EU6DR7055659040-6LBDP1B  
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 70° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4919.4 lumens  
Efficiency: N/A  
Efficacy: 67.6 lumens/watt  
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct


Input Watts (W): 72.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



Downlight

TEST NUMBER: P770168  
CATALOG NUMBER: LD6D65D010-EU6DR7055659040-6LBDP1B

### Luminous Intensity Polar Plot





TEST NUMBER: P770168

CATALOG NUMBER: LD6D65D010-EU6DR7055659040-6LBDP1B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10		0		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	604299
5°	586339
10°	569998
15°	562521
20°	525274
25°	394616
30°	278960
35°	98810
40°	51960
45°	55348
50°	57300
55°	58385
60°	58739
65°	57498
70°	54276
75°	50278
80°	44611
85°	36230

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 57.5°  
 Luminance: 58769 cd/sqm



TEST NUMBER: P770168

CATALOG NUMBER: LD6D65D010-EU6DR7055659040-6LBDP1B

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	504.2	10.3
10°-20°	1383.1	28.1
20°-30°	1523.3	31.0
30°-40°	582.0	11.8
40°-50°	274.8	5.6
50°-60°	273.2	5.6
60°-70°	218.8	4.4
70°-80°	125.7	2.6
80°-90°	34.2	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3410.7	69.3
0°-40°	3992.7	81.2
0°-60°	4540.7	92.3
0°-90°	4919.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4919.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	5531	
5°	5346	504
15°	4973	1383
25°	3273	1523
35°	741	582
45°	358	275
55°	306	273
65°	222	219
75°	119	126
85°	29	34
90°	0	



TEST NUMBER: P770168

CATALOG NUMBER: LD6D65D010-EU6DR7055659040-6LBDP1B

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	5530.8
2.5°	5473.0
5°	5346.0
7.5°	5240.0
10°	5137.6
12.5°	5050.9
15°	4973.0
17.5°	4784.7
20°	4517.6
22.5°	3941.4
25°	3273.3
27.5°	2849.4
30°	2211.1
32.5°	1428.2
35°	740.8
37.5°	400.2
40°	364.3
42.5°	361.7
45°	358.2
47.5°	350.3
50°	337.1
52.5°	322.2
55°	306.5
57.5°	289.0
60°	268.8
62.5°	246.1
65°	222.4
67.5°	196.2
70°	169.9
72.5°	143.6
75°	119.1
77.5°	93.7
80°	70.9
82.5°	49.9
85°	28.9
87.5°	11.4
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)