

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P766569

Luminaire Tested: LD6D45BD010-EU6DR4040509035-6LBDP1LI

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P766569
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-28)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D45BD010-EU6DR4040509035-6LBDP1LI
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 40° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5431.7 lumens
Efficiency: N/A
Efficacy: 140.4 lumens/watt
Spacing Criteria (0/90/45): 0.68 / 0.68 / 0.6
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 38.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P766569
CATALOG NUMBER: LD6D45BD010-EU6DR4040509035-6LBDP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P766569

CATALOG NUMBER: LD6D45BD010-EU6DR4040509035-6LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20																	
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR																																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100									100																		
1	115	112	110	108	112	110	108	107	106	105	103	103	101	100	99	98	97	96									96																		
2	110	106	103	100	108	105	102	99	102	99	97	99	97	95	96	95	93	92									92																		
3	106	101	97	94	104	100	96	93	97	94	92	95	93	90	93	91	89	88									88																		
4	102	97	92	89	101	95	91	88	93	90	87	92	89	86	90	87	85	84									84																		
5	99	92	88	84	97	91	87	84	90	86	83	88	85	83	87	84	82	81									81																		
6	95	88	84	80	94	88	83	80	86	82	80	85	82	79	84	81	79	77									77																		
7	92	85	80	77	91	84	80	77	83	79	76	82	79	76	81	78	76	74									74																		
8	89	82	77	74	88	81	77	74	80	76	73	79	76	73	78	75	73	72									72																		
9	86	79	74	71	85	78	74	71	77	73	71	76	73	70	76	72	70	69									69																		
10	83	76	71	68	82	75	71	68	75	71	68	74	70	68	73	70	68	67									67																		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1381777
5°	1375056
10°	1299736
15°	1104930
20°	753088
25°	314217
30°	98799
35°	45924
40°	25388
45°	11651
50°	5643
55°	3105
60°	1617
65°	569
70°	224
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 11651 cd/sqm



TEST NUMBER: P766569

CATALOG NUMBER: LD6D45BD010-EU6DR4040509035-6LBDP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1170.7	21.6
10°-20°	2622.6	48.3
20°-30°	1312.8	24.2
30°-40°	240.6	4.4
40°-50°	66.4	1.2
50°-60°	15.6	0.3
60°-70°	3.0	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5106.0	94.0
0°-40°	5346.7	98.4
0°-60°	5428.6	99.9
0°-90°	5431.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5431.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	12647	
5°	12537	###
15°	9768	2623
25°	2606	1313
35°	344	241
45°	75	66
55°	16	16
65°	2	3
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P766569

CATALOG NUMBER: LD6D45BD010-EU6DR4040509035-6LBDP1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	12646.6
2.5°	12628.1
5°	12537.2
7.5°	12247.6
10°	11715.0
12.5°	10884.6
15°	9768.2
17.5°	8316.5
20°	6476.9
22.5°	4415.7
25°	2606.4
27.5°	1377.8
30°	783.1
32.5°	506.1
35°	344.3
37.5°	246.0
40°	178.0
42.5°	121.9
45°	75.4
47.5°	48.0
50°	33.2
52.5°	23.6
55°	16.3
57.5°	10.3
60°	7.4
62.5°	4.4
65°	2.2
67.5°	1.5
70°	0.7
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)