

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P758559

Luminaire Tested: LD6D05D010-EU6DR550210IC9030-6LBS1MW

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P758559  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-52)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD6D05D010-EU6DR550210IC9030-6LBS1MW  
Description: 6 INCH ROUND SHALLOW MATTE WHITE TRIM, WITH 55° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 675.8 lumens  
Efficiency: N/A  
Efficacy: 90.1 lumens/watt  
Spacing Criteria (0/90/45): 0.89 / 0.89 / 0.87  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 7.5  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight



TEST NUMBER: P758559

CATALOG NUMBER: LD6D05D010-EU6DR550210IC9030-6LBS1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P758559

CATALOG NUMBER: LD6D05D010-EU6DR550210IC9030-6LBS1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94					94			
2	108	103	99	96	106	101	98	95	98	95	92	95	93	90	92	90	89	87					87			
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81					81			
4	97	90	84	80	95	88	83	79	86	82	78	84	81	78	82	79	77	75					75			
5	92	84	78	74	91	83	77	73	81	76	73	79	75	72	78	74	71	70					70			
6	88	79	73	68	86	78	72	68	76	71	68	75	70	67	74	70	67	65					65			
7	83	74	68	64	82	73	67	63	72	67	63	71	66	63	70	65	62	61					61			
8	79	69	63	59	78	69	63	59	68	63	59	67	62	59	66	62	58	57					57			
9	75	66	60	56	74	65	59	55	64	59	55	63	58	55	62	58	55	54					54			
10	72	62	56	52	71	61	56	52	61	56	52	60	55	52	59	55	52	50					50			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	82798
5°	79517
10°	79216
15°	76930
20°	68985
25°	57011
30°	43072
35°	31225
40°	19982
45°	9132
50°	2975
55°	1295
60°	546
65°	78
70°	0
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 9132 cd/sqm



TEST NUMBER: P758559

CATALOG NUMBER: LD6D05D010-EU6DR550210IC9030-6LBS1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	69.0	10.2
10°-20°	188.3	27.9
20°-30°	214.6	31.7
30°-40°	146.1	21.6
40°-50°	50.3	7.4
50°-60°	6.9	1.0
60°-70°	0.7	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	471.8	69.8
0°-40°	617.9	91.4
0°-60°	675.2	99.9
0°-90°	675.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	675.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	758	
5°	725	69
15°	680	188
25°	473	215
35°	234	146
45°	59	50
55°	7	7
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P758559

CATALOG NUMBER: LD6D05D010-EU6DR550210IC9030-6LBS1MW

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	757.8
2.5°	740.5
5°	725.0
7.5°	717.4
10°	714.0
12.5°	702.7
15°	680.1
17.5°	644.4
20°	593.3
22.5°	534.3
25°	472.9
27.5°	409.0
30°	341.4
32.5°	284.1
35°	234.1
37.5°	186.6
40°	140.1
42.5°	97.1
45°	59.1
47.5°	31.9
50°	17.5
52.5°	10.4
55°	6.8
57.5°	4.3
60°	2.5
62.5°	1.1
65°	0.3
67.5°	0.1
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)