

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P770741

Luminaire Tested: LD6D70BD010-EU6DR6070959024-6LBDP1H

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P770741
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D70BD010-EU6DR6070959024-6LBDP1H
Description: 6 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6936.2 lumens
Efficiency: N/A
Efficacy: 104.1 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 66.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P770741
CATALOG NUMBER: LD6D70BD010-EU6DR6070959024-6LBDP1H

Luminous Intensity Polar Plot





TEST NUMBER: P770741

CATALOG NUMBER: LD6D70BD010-EU6DR6070959024-6LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93			93																
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86			86																
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80			80																
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75			75																
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70			70																
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66			66																
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62			62																
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59			59																
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55			55																
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53			53																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	900046
5°	922174
10°	933313
15°	889107
20°	783923
25°	634052
30°	428880
35°	214920
40°	34859
45°	34118
50°	34812
55°	35336
60°	36318
65°	37151
70°	38015
75°	38458
80°	37123
85°	30965

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 38458 cd/sqm



TEST NUMBER: P770741

CATALOG NUMBER: LD6D70BD010-EU6DR6070959024-6LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	803.6	11.6
10°-20°	2174.2	31.3
20°-30°	2339.2	33.7
30°-40°	1016.8	14.7
40°-50°	170.8	2.5
50°-60°	166.1	2.4
60°-70°	142.0	2.0
70°-80°	95.0	1.4
80°-90°	28.4	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5317.0	76.7
0°-40°	6333.8	91.3
0°-60°	6670.7	96.2
0°-90°	6936.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6936.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8238	
5°	8408	804
15°	7860	2174
25°	5259	2339
35°	1611	1017
45°	221	171
55°	186	166
65°	144	142
75°	91	95
85°	25	28
90°	0	



TEST NUMBER: P770741

CATALOG NUMBER: LD6D70BD010-EU6DR6070959024-6LBDP1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	8237.6
2.5°	8469.1
5°	8408.0
7.5°	8427.3
10°	8412.3
12.5°	8238.6
15°	7860.2
17.5°	7352.1
20°	6742.1
22.5°	6089.2
25°	5259.4
27.5°	4206.7
30°	3399.4
32.5°	2620.1
35°	1611.3
37.5°	689.3
40°	244.4
42.5°	225.1
45°	220.8
47.5°	213.3
50°	204.8
52.5°	195.1
55°	185.5
57.5°	175.8
60°	166.2
62.5°	155.4
65°	143.7
67.5°	131.9
70°	119.0
72.5°	105.1
75°	91.1
77.5°	75.0
80°	59.0
82.5°	41.8
85°	24.7
87.5°	8.6
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)