

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P770819

Luminaire Tested: LD6D70BD010-EU6DR6570959024-6LBDP1H

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P770819
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D70BD010-EU6DR6570959024-6LBDP1H
Description: 6 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6060.6 lumens
Efficiency: N/A
Efficacy: 91.0 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 66.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P770819
CATALOG NUMBER: LD6D70BD010-EU6DR6570959024-6LBDP1H

Luminous Intensity Polar Plot





TEST NUMBER: P770819
 CATALOG NUMBER: LD6D70BD010-EU6DR6570959024-6LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93																			
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87																			
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80																			
4	97	89	84	79	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	83	78	73	90	83	77	73	81	76	72	79	75	72	77	74	71	69																			
6	87	78	72	68	86	77	72	68	76	71	67	74	70	67	73	69	66	65																			
7	83	73	67	63	81	73	67	63	71	66	62	70	66	62	69	65	62	60																			
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	57																			
9	75	65	59	55	74	65	59	55	64	58	55	63	58	55	62	58	54	53																			
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	651970
5°	652508
10°	675485
15°	676598
20°	622920
25°	530759
30°	406322
35°	287053
40°	169444
45°	68791
50°	24936
55°	13887
60°	7976
65°	4395
70°	4600
75°	3588
80°	3712
85°	3134

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 68791 cd/sqm



TEST NUMBER: P770819

CATALOG NUMBER: LD6D70BD010-EU6DR6570959024-6LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	574.6	9.5
10°-20°	1657.4	27.3
20°-30°	1988.6	32.8
30°-40°	1336.4	22.1
40°-50°	400.1	6.6
50°-60°	70.6	1.2
60°-70°	20.1	0.3
70°-80°	9.8	0.2
80°-90°	3.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4220.6	69.6
0°-40°	5556.9	91.7
0°-60°	6027.6	99.5
0°-90°	6060.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6060.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5967	
5°	5949	575
15°	5982	1657
25°	4403	1989
35°	2152	1336
45°	445	400
55°	73	71
65°	17	20
75°	8	10
85°	2	3
90°	0	



TEST NUMBER: P770819
CATALOG NUMBER: LD6D70BD010-EU6DR6570959024-6LBDP1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	5967.1
2.5°	5992.5
5°	5949.3
7.5°	6039.2
10°	6088.4
12.5°	6076.5
15°	5981.5
17.5°	5749.2
20°	5357.4
22.5°	4896.1
25°	4402.6
27.5°	3845.5
30°	3220.6
32.5°	2654.1
35°	2152.1
37.5°	1656.1
40°	1188.0
42.5°	775.9
45°	445.2
47.5°	235.7
50°	146.7
52.5°	101.8
55°	72.9
57.5°	52.6
60°	36.5
62.5°	23.7
65°	17.0
67.5°	15.3
70°	14.4
72.5°	11.0
75°	8.5
77.5°	7.6
80°	5.9
82.5°	4.2
85°	2.5
87.5°	1.7
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)