

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P758331

Luminaire Tested: LD6D05D010-EU6DR400210IC9035-6LBDP1B

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P758331
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-28)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D05D010-EU6DR400210IC9035-6LBDP1B
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 40° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 649.0 lumens
Efficiency: N/A
Efficacy: 86.5 lumens/watt
Spacing Criteria (0/90/45): 0.68 / 0.68 / 0.6
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 7.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P758331

CATALOG NUMBER: LD6D05D010-EU6DR400210IC9035-6LBDP1B

Luminous Intensity Polar Plot





TEST NUMBER: P758331

CATALOG NUMBER: LD6D05D010-EU6DR400210IC9035-6LBDP1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20								
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR	0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	99	98	97	96	96	95	93	92																
	1	115	112	110	108	112	110	108	107	106	105	103	103	101	100	99	98	97	96	95	93	92	91	89	88	87	85	84	81																
	2	110	106	103	100	108	105	102	99	102	99	97	99	97	95	96	95	93	92	91	89	88	87	85	84	82	81	79	77																
	3	106	101	97	94	104	100	96	93	97	94	92	95	93	90	93	91	89	88	87	85	84	82	81	79	77	76	74	72																
	4	102	97	92	89	101	95	91	88	93	90	87	92	89	86	90	87	85	84	82	81	79	77	76	74	72	71	69	67																
	5	99	92	88	84	97	91	87	84	90	86	83	88	85	83	87	84	82	81	79	77	76	74	72	71	69	67	65	63																
	6	95	88	84	80	94	88	83	80	86	82	80	85	82	79	84	81	79	77	76	74	72	71	69	67	65	63	61	59																
	7	92	85	80	77	91	84	80	77	83	79	76	82	79	76	81	78	76	74	72	71	69	67	65	63	61	59	57	55	53															
	8	89	82	77	74	88	81	77	74	80	76	73	79	76	73	78	75	73	72	71	69	67	65	63	61	59	57	55	53	51															
	9	86	79	74	71	85	78	74	71	77	73	71	76	73	70	76	72	70	69	67	65	63	61	59	57	55	53	51	49	47															
	10	83	76	71	68	82	75	71	68	75	71	68	74	70	68	73	70	68	67	65	63	61	59	57	55	53	51	49	47	45															

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	165104
5°	164298
10°	155303
15°	132028
20°	89984
25°	37553
30°	11809
35°	5482
40°	3038
45°	1391
50°	680
55°	362
60°	197
65°	78
70°	32
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1391 cd/sqm



TEST NUMBER: P758331

CATALOG NUMBER: LD6D05D010-EU6DR400210IC9035-6LBDP1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	139.9	21.6
10°-20°	313.4	48.3
20°-30°	156.9	24.2
30°-40°	28.7	4.4
40°-50°	7.9	1.2
50°-60°	1.9	0.3
60°-70°	0.4	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	610.1	94.0
0°-40°	638.8	98.4
0°-60°	648.7	99.9
0°-90°	649.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	649.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1511	
5°	1498	140
15°	1167	313
25°	312	157
35°	41	29
45°	9	8
55°	2	2
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P758331

CATALOG NUMBER: LD6D05D010-EU6DR400210IC9035-6LBDP1B

CANDELA DISTRIBUTION (FULL):

0°	
0°	1511.1
2.5°	1508.9
5°	1498.0
7.5°	1463.4
10°	1399.8
12.5°	1300.5
15°	1167.2
17.5°	993.7
20°	773.9
22.5°	527.6
25°	311.5
27.5°	164.6
30°	93.6
32.5°	60.4
35°	41.1
37.5°	29.4
40°	21.3
42.5°	14.6
45°	9.0
47.5°	5.7
50°	4.0
52.5°	2.8
55°	1.9
57.5°	1.3
60°	0.9
62.5°	0.5
65°	0.3
67.5°	0.2
70°	0.1
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)