

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P758800

Luminaire Tested: LD6D05D010-EU6DR700210IC9035-6LBDP1H

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P758800
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D05D010-EU6DR700210IC9035-6LBDP1H
Description: 6 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 704.2 lumens
Efficiency: N/A
Efficacy: 93.9 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 7.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P758800
CATALOG NUMBER: LD6D05D010-EU6DR700210IC9035-6LBDP1H

Luminous Intensity Polar Plot





TEST NUMBER: P758800

CATALOG NUMBER: LD6D05D010-EU6DR700210IC9035-6LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

0°	
0°	86502
5°	83926
10°	81590
15°	80515
20°	75194
25°	56492
30°	39931
35°	14152
40°	7431
45°	7927
50°	8193
55°	8363
60°	8413
65°	8247
70°	7763
75°	7219
80°	6355
85°	5140

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 8419 cd/sqm



TEST NUMBER: P758800

CATALOG NUMBER: LD6D05D010-EU6DR700210IC9035-6LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	72.2	10.2
10°-20°	198.0	28.1
20°-30°	218.1	31.0
30°-40°	83.3	11.8
40°-50°	39.3	5.6
50°-60°	39.1	5.6
60°-70°	31.3	4.4
70°-80°	18.0	2.6
80°-90°	4.9	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	488.2	69.3
0°-40°	571.5	81.2
0°-60°	650.0	92.3
0°-90°	704.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	704.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	792	
5°	765	72
15°	712	198
25°	469	218
35°	106	83
45°	51	39
55°	44	39
65°	32	31
75°	17	18
85°	4	5
90°	0	



TEST NUMBER: P758800

CATALOG NUMBER: LD6D05D010-EU6DR700210IC9035-6LBDP1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	791.7
2.5°	783.4
5°	765.2
7.5°	750.1
10°	735.4
12.5°	723.0
15°	711.8
17.5°	684.9
20°	646.7
22.5°	564.2
25°	468.6
27.5°	407.9
30°	316.5
32.5°	204.4
35°	106.1
37.5°	57.3
40°	52.1
42.5°	51.8
45°	51.3
47.5°	50.1
50°	48.2
52.5°	46.1
55°	43.9
57.5°	41.4
60°	38.5
62.5°	35.2
65°	31.9
67.5°	28.1
70°	24.3
72.5°	20.6
75°	17.1
77.5°	13.4
80°	10.1
82.5°	7.2
85°	4.1
87.5°	1.6
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)