

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P770753

Luminaire Tested: LD6D70BD010-EU6DR6070959027-6LBDP1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P770753
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D70BD010-EU6DR6070959027-6LBDP1B
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6187.3 lumens
Efficiency: N/A
Efficacy: 92.9 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 66.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P770753
CATALOG NUMBER: LD6D70BD010-EU6DR6070959027-6LBDP1B

Luminous Intensity Polar Plot





TEST NUMBER: P770753

CATALOG NUMBER: LD6D70BD010-EU6DR6070959027-6LBDP1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93																			
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86																			
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80																			
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70																			
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66																			
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62																			
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59																			
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55																			
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	802870
5°	822619
10°	832552
15°	793118
20°	699288
25°	565600
30°	382578
35°	191711
40°	31093
45°	30440
50°	31055
55°	31507
60°	32385
65°	33118
70°	33894
75°	34321
80°	33096
85°	27580

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 34321 cd/sqm



TEST NUMBER: P770753

CATALOG NUMBER: LD6D70BD010-EU6DR6070959027-6LBDP1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	716.8	11.6
10°-20°	1939.4	31.3
20°-30°	2086.7	33.7
30°-40°	907.0	14.7
40°-50°	152.3	2.5
50°-60°	148.1	2.4
60°-70°	126.7	2.0
70°-80°	84.8	1.4
80°-90°	25.4	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4743.0	76.7
0°-40°	5650.0	91.3
0°-60°	5950.4	96.2
0°-90°	6187.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6187.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7348	
5°	7500	717
15°	7012	1939
25°	4692	2087
35°	1437	907
45°	197	152
55°	165	148
65°	128	127
75°	81	85
85°	22	25
90°	0	



TEST NUMBER: P770753

CATALOG NUMBER: LD6D70BD010-EU6DR6070959027-6LBDP1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	7348.2
2.5°	7554.8
5°	7500.3
7.5°	7517.5
10°	7504.1
12.5°	7349.2
15°	7011.6
17.5°	6558.3
20°	6014.2
22.5°	5431.8
25°	4691.6
27.5°	3752.5
30°	3032.4
32.5°	2337.2
35°	1437.3
37.5°	614.9
40°	218.0
42.5°	200.8
45°	197.0
47.5°	190.3
50°	182.7
52.5°	174.0
55°	165.4
57.5°	156.8
60°	148.2
62.5°	138.7
65°	128.1
67.5°	117.6
70°	106.1
72.5°	93.7
75°	81.3
77.5°	66.9
80°	52.6
82.5°	37.3
85°	22.0
87.5°	7.7
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)