

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P758285

Luminaire Tested: LD6D05D010-EU6DR350210IC9050-6LBS1LI

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P758285
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-20)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D05D010-EU6DR350210IC9050-6LBS1LI
Description: 6 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 35° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 747.9 lumens
Efficiency: N/A
Efficacy: 99.7 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.54
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 7.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P758285
CATALOG NUMBER: LD6D05D010-EU6DR350210IC9050-6LBS1LI

Luminous Intensity Polar Plot





TEST NUMBER: P758285

CATALOG NUMBER: LD6D05D010-EU6DR350210IC9050-6LBS1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20																	
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR																																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100									100																		
1	115	112	110	108	112	110	108	107	106	105	103	103	101	100	99	98	98	96									96																		
2	110	106	103	101	108	105	102	99	102	99	97	99	97	95	96	95	93	92									92																		
3	106	101	97	94	105	100	96	94	97	95	92	95	93	91	93	91	89	88									88																		
4	103	97	92	89	101	96	92	89	94	90	88	92	89	87	90	88	86	84									84																		
5	99	93	88	85	98	92	87	84	90	86	84	89	85	83	87	84	82	81									81																		
6	96	89	84	81	94	88	84	81	87	83	80	85	82	80	84	81	79	78									78																		
7	93	85	81	78	91	85	80	77	84	80	77	83	79	77	82	79	76	75									75																		
8	90	82	78	74	88	82	77	74	81	77	74	80	76	74	79	76	73	72									72																		
9	87	79	75	72	86	79	75	72	78	74	71	77	74	71	77	73	71	70									70																		
10	84	77	72	69	83	76	72	69	76	72	69	75	71	69	74	71	69	68									68																		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	224848
5°	219554
10°	197884
15°	153588
20°	87112
25°	33888
30°	12642
35°	6936
40°	4521
45°	2750
50°	1751
55°	1238
60°	896
65°	491
70°	32
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2750 cd/sqm



TEST NUMBER: P758285

CATALOG NUMBER: LD6D05D010-EU6DR350210IC9050-6LBS1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	184.1	24.6
10°-20°	359.5	48.1
20°-30°	146.6	19.6
30°-40°	35.1	4.7
40°-50°	14.6	2.0
50°-60°	6.0	0.8
60°-70°	1.9	0.3
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	690.2	92.3
0°-40°	725.3	97.0
0°-60°	745.9	99.7
0°-90°	747.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	747.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2058	
5°	2002	184
15°	1358	359
25°	281	147
35°	52	35
45°	18	15
55°	6	6
65°	2	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P758285

CATALOG NUMBER: LD6D05D010-EU6DR350210IC9050-6LBS1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	2057.9
2.5°	2045.5
5°	2001.8
7.5°	1914.8
10°	1783.6
12.5°	1598.9
15°	1357.8
17.5°	1063.0
20°	749.2
22.5°	477.7
25°	281.1
27.5°	158.9
30°	100.2
32.5°	70.4
35°	52.0
37.5°	40.2
40°	31.7
42.5°	24.5
45°	17.8
47.5°	13.3
50°	10.3
52.5°	8.2
55°	6.5
57.5°	5.3
60°	4.1
62.5°	3.0
65°	1.9
67.5°	0.7
70°	0.1
72.5°	0.1
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.1
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)